







RoHS



PCB Layout(Pattern side)



Circuit Diagram



Product No. : TS-095TS-□□-□□

型号:

□: 包装方式
-P=编带(非编带, 不启用)
□: 弹片
D2=SUS/1PCS

操作力度:

120=120gf±50gf
180=180gf±50gf
250=250gf±50gf

□: 脚距

(C80=L8.0) L1=10
(C85=L8.5) L1=11
(C90=L9.0) L1=11
(C95=L9.5) L1=12

⑤	Terminal		4	Brass	Silvering
④	Reed		1	SUS	Silver covered
③	Base		1	PPA	Black
②	Cover		1	SPCC	Plating Cu Sn
①	Keystoke		1	PPA	Black
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
众迪

Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-095TS-□□-D□
Approved	date		

Drawing number:

Proportion 1:1 unit mm gage number A4

modify Review Approved

Tolerance not specified

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
机械性能 Mechanical Properties	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
	机械寿命 Mechanical life:	200,000 cycles Min
环境性能 Environmental	操作行程 Operation Stroke:	0.25±0.10mm
	工作温度 Operation temperature:	-25℃~ +75℃
可靠性特性 Reliability Characteristics	使用湿度 Use humidity:	≤85% RH
	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
应用领域 Application area	手工焊 Manual welding:	≥260℃ 时间 Time 3s
	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试




耐电压测试



回流焊机



二次元测量



高精密寿命测试



盐雾测试



按键荷重曲线仪

ZHONGDI® Zhongdi Electronic Technology Co., Ltd											
design		date		name		TACT SWITCHS					
Review		date		name		TS-095TS-□□-D□					
Approved		date		name		TS-095TS-□□-D□					
number:											
1:1		unit	mm	gape number				A4			