






RoHS



PCB Layout(Pattern side)



Circuit Diagram



TOTAL HEIGHT	
Code	H
025	2.5
027	2.7
031	3.1
034	3.4
037	3.7
043	4.3
050	5.0
055	5.5

Product No. : TS-080S-□□-□□

型号:

产品高度 (H) :

025=2.5mm

027=2.7mm

031=3.1mm

□□: 包装方式

-P=编带(非编带, 不启用)

□□: 弹片

D2=SUS/1PCS

操作力度:

120=120gf±50gf

180=180gf±50gf

250=250gf±50gf

(E)	Terminal		4	Brass	Silvering
(D)	Contact		1	SUS	Silver covered
(C)	Base		1	PPA	Black
(B)	Cover		1	Brass	Plating Cu Sn
(A)	Knob		1	PPA	
NO.	Name	Number	Qty	Materil	Remarks

ZHONGDI®
众迪

Zhongdi Electronic Technology Co., Ltd

design	date	name	TACT SWITCHS
Review	date	model	TS-080S-□□-D□
Approved	date		

Drawing number:

modify Review Approved Tolerance not specified Proportion 1:1 unit mm gage number A4

项 目 Item	技术参数 Technical Parameter	标 准 Standard
电气性能 Electrical Properties	额定电流 Rated Current:	50mA
	额定电压 Rated voltage:	DC 12V
	接触电阻 Contact resistance:	≤100mΩ
	绝缘电阻 Insulation Resistance:	DC 250V 1 min ≥100MΩ
	耐压强度 Compressive strength:	AC 250V 50Hz/1 min
机械性能 Mechanical Properties	机械寿命 Mechanical life:	200,000 cycles Min
	操作行程 Operation Stroke:	0.25±0.10mm
环境性能 Environmental	工作温度 Operation temperature:	-25℃~ +75℃
	使用湿度 Use humidity:	≤85% RH
可靠性特性 Reliability Characteristics	回流焊 Reflow Soldering:	≤260℃ 时间 Time 3s
	波峰焊 Wave soldering:	
	手工焊 Manual welding:	≥260℃ 时间 Time 3s
应用领域 Application area	影音产品、电子玩具、数码产品、通讯产品、安防产品等. Audiovisual products, electronic toys, digital products, communication products, security products, etc	



绝缘电阻测量仪



直流低电阻测试仪




耐电压测试



回流焊



二次元测量仪



高精密寿命测试仪



盐雾测试仪



按键荷重曲线仪

ZHONGDI® 众迪										Zhongdi Electronic Technology Co., Ltd											
design			date			name			TACT SWITCHS												
Review			date			model			TS-080S-□□-D□												
Approved			date																		
number:																					
1:1		unit		mm		gape number												A4			