








Product NO.		DOSIN-801-0184		
REV	DESCRIPTION	DMN	DATE	APPROVEN
A	First issue	JIM	2012/11/02	John kine



Specifications

Impedance: 50 Ohms
Frequency Range: DC~3G
VSWR: 1.3MAX
Working Voltage: 500V rms @ sea level
Insulation Resistance: 5000 Ohms min
Temperature Range: -55°C T0 +155°C
Relative Temperature: ≤95% (40°C ±2°C)
Drawings products are in line with ROHS standards



PCB

1	Body	Zinc	NI:80-120u"
2	Center contact	Brass	AU:1u"
3	Lead	Iron	AU:1u"
4	Fixed footrest	Iron	NI:80-120u"
5	Insulator	POM	White
6	Fixed mount	PBT	White
7	Washer	Brass	NI:80-120u"
8	Hex nut	Brass	NI:80-120u"
9			
10			
NO	Component Number	Material	Finish

NOTE:

Tolerance

0-6
6-30
30-120
Angular
±0.20
±0.30
±0.5
±2°



Name: BNC WHITE JACK CONNECTOR (11.8MM)

SIZE A Product NO.

Datetime 2012/11/02

CAD FILE D/company drawings/BD

SHEET: 1 OF 1

Dosin Industrial(H.K)Co.Ltd
E-mail: dosin2005@163.com
dosin2005@dosin-china.com
dosin2005@dosin-china.com
Web: http://www.dosin.com
TEL: (0086)769-81153906
FAX: (0086)769-81875836

Dosin Hardware Electronics Co.,Ltd