

Features

- Low operating voltage: 18V
- Peak Pulse Power (8/20 μ s):220W
- Ultra low leakage: nA level
- Low clamping voltage
- -IEC 61000-4-2 (ESD) immunity test
Air discharge: ± 30 kV
Contact discharge: ± 30 kV
- -IEC61000-4-4 (EFT) 40A (5/50ns)
- 3-pin leadless package
- These are Pb-Free Devices
- Response Time is Typically < 1 ns


Mechanical Characteristics

- Package: SOT-23
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound
- Terminal Connections: See Diagram Below
- -IEC 61000-4-2 (ESD) immunity test

Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation
- Peripherals

Dimensions and Pin Configuration



SOT-23


Absolute Maximum Ratings (Tamb=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20μs)	Ppk	220	W
Peak Pulse Current (8/20μs)	Ipp	6	A
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	VESD	±30 ±30	KV
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	-55 to +150	°C

Electrical Characteristics (TA=25°C unless otherwise specified)

Parameter	Symbol	Min	Typ	Max	Unit	Test Condition
Reverse Working Voltage	VRWM	--	--	18	V	
Breakdown Voltage	VBR	20	--	24	V	IT= 1mA
Reverse Leakage Current	IR	--	--	0.1	uA	VRWM=18V
Forward Voltage	VF	--	0.7	1.2	V	IF = 1mA
Clamping Voltage	VC	--	30	--	V	Ipp=1A(8x 20us pulse)
Clamping Voltage	VC	--	--	35	V	Ipp=6A(8x 20us pulse)
Junction Capacitance	CJ	--	--	20	pF	VR =0V, f =1MHz, Pin1 to Pin2
Junction Capacitance	CJ	--	--	40	pF	VR =0V, f =1MHz, Pin1,2 to Pin3

Symbol	Parameter
I _{PP}	Maximum Reverse Peak Pulse Current
V _C	Clamping Voltage @ I _{PP}
V _{RWM}	Working Peak Reverse Voltage
I _R	Maximum Reverse Leakage Current @ V _{RWM}
V _{BR}	Breakdown Voltage @ I _T
I _T	Test Current
I _F	Forward Current
V _F	Forward Voltage @ I _F
P _{pk}	Peak Power Dissipation
C	Capacitance @ V _R = 0 and f = 1.0 MHz



Characteristic Curves

Fig1. 8/20 μ s Pulse Waveform




Fig2. ESD Pulse Waveform (according to IEC 61000-4-2)






Fig3. Power Derating Curve



Package Outline Dimensions (unit: mm)

SOT-23



Mounting Pad Layout (unit: mm)

