

BCQ120N16M1

N-Channel Silicon Carbide Power MOSFET

1200 V, 166 A, 16 mΩ



Features

- High switching speed with a low gate charge
- Fast intrinsic diode with low reverse recovery
- Robust Avalanche Capability
- 100% Avalanche Tested
- Pb-free, Halogen Free, and RoHS Compliant



$BV_{DSS}, T_c=25^{\circ}C$	$I_D, T_c=25^{\circ}C$	$R_{DS(on),typ}$	$Q_{g,typ}$
1200 V	166 A	16 mΩ	152 nC

Benefits

- System efficiency improvement
- Higher frequency applicability
- Increased power density
- Reduced cooling effort

Applications

- Solar inverter
- EV charging station
- UPS
- Industrial power supply



Absolute Maximum Ratings ($T_C = 25^{\circ}C$ unless otherwise noted)

Symbol	Parameter		Value	Unit
V_{DSS}	Drain to Source Voltage		1200	V
V_{GS}	Gate to Source Voltage (DC)		-10 / +22	V
V_{GSop}	Recommended Operation Value		-5...-3 / +18	V
I_D	Drain Current	Continuous ($T_C = 25^{\circ}C$) (Note1)	166	A
		Continuous ($T_C = 110^{\circ}C$)	109	
I_{DM}	Drain Current	Pulsed (Note1)	416	A
P_D	Power Dissipation	($T_C = 25^{\circ}C$)	710	W
		Derate Above 25°C	4.73	W/°C
T_J, T_{STG}	Operating and Storage Temperature Range		-55 to 175	°C

Thermal Characteristics

Symbol	Parameter	Value	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case, Max.	0.21	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient, Max.	40	
T_{sld}	Soldering temperature, wave soldering only allowed at leads	260	°C

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
--------	-----------	-----------------	-----	-----	-----	------

Off Characteristics

BV_{DSS}	Drain to Source Breakdown Voltage	$V_{GS} = 0\text{ V}, I_D = 1\text{ mA}$	1200			V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}$		1	100	μA
		$V_{DS} = 1200\text{ V}, V_{GS} = 0\text{ V}, T_J = 175^\circ\text{C}$		10		
I_{GSS}	Gate-Source Leakage Current	$V_{GS} = +22\text{ V}, V_{DS} = 0\text{ V}$			+100	nA
		$V_{GS} = -10\text{ V}, V_{DS} = 0\text{ V}$			-100	

On Characteristics

$V_{GS(th)}$	Gate Threshold Voltage	$V_{GS} = V_{DS}, I_D = 24\text{ mA}$ (tested after $V_{GS} = 22\text{ V}, 1\text{ ms pulse}$)	2.0	3.0	4.5	V
$R_{DS(on)}$	Static Drain to Source On Resistance	$V_{GS} = 18\text{ V}, I_D = 50\text{ A}$		16.0	22.4	mΩ
		$V_{GS} = 18\text{ V}, I_D = 50\text{ A}, T_J = 175^\circ\text{C}$		25.6		
		$V_{GS} = 15\text{ V}, I_D = 50\text{ A}$		21.5		
g_{fs}	Transconductance	$V_{DS} = 20\text{ V}, I_D = 50\text{ A}$		32.7		S

Dynamic Characteristics

C_{iss}	Input Capacitance	$V_{DS} = 800\text{ V}, V_{GS} = 0\text{ V}, f = 250\text{ kHz}$		4063		pF
C_{oss}	Output Capacitance			227		
C_{rss}	Reverse Capacitance			3		
E_{oss}	Stored Energy in Output Capacitance	$V_{DS} = 0\text{ V to } 800\text{ V}, V_{GS} = 0\text{ V}$		94		μJ
$C_{o(er)}$	Energy Related Output Capacitance			295		pF
$C_{o(tr)}$	Time Related Output Capacitance			476		
$Q_{g(tot)}$	Total Gate Charge	$V_{DS} = 800\text{ V}, I_D = 50\text{ A},$ $V_{GS} = -3\text{ V} / 18\text{ V},$ Inductive load		152		nC
Q_{gs}	Gate to Source Charge			49		
Q_{gd}	Gate to Drain "Miller" Charge			29		
R_G	Internal Gate Resistance	$f = 1\text{ MHz}, V_{AC} = 30\text{ mV}$		2.7		Ω

Switching Characteristics

$t_{d(on)}$	Turn-on Delay Time	$V_{DS} = 800\text{ V}, I_D = 50\text{ A},$ $V_{GS} = -3\text{ V} / 18\text{ V}, R_G = 4.7\text{ }\Omega,$ FWD : BCH120S20D2, Inductive load		34		ns
t_r	Turn-on Rise Time			54		
$t_{d(off)}$	Turn-off Delay Time			68		
t_f	Turn-off Fall Time			13		
E_{on}	Turn-on Switching Energy			1325		μJ
E_{off}	Turn-off Switching Energy			455		
E_{tot}	Total Switching Energy			1780		

Electrical Characteristics ($T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
--------	-----------	-----------------	-----	-----	-----	------

Source-Drain Diode Characteristics

I_S	Continuous Diode Forward Current	$V_{GS} = -3\text{ V}$ (Note1)			166	A
I_{SM}	Pulsed Diode Forward Current	$V_{GS} = -3\text{ V}$ (Note1)			416	
V_{SD}	Diode Forward Voltage	$V_{GS} = -3\text{ V}, I_{SD} = 50\text{ A}$		4.0		V
t_{rr}	Reverse Recovery Time	$V_{DD} = 800\text{ V}, I_{SD} = 50\text{ A},$ $di_F/dt = 1200\text{ A}/\mu\text{s},$ Includes Q_{oss}		43		ns
Q_{rr}	Reverse Recovery Charge			420		nC
I_{rrm}	Peak Reverse Recovery Current			17		A

※Note 1 : Limited by maximum junction temperature.

Typical Performance Characteristics

Figure 1. On-Region Characteristics $T_J = -40^{\circ}\text{C}$




Figure 2. On-Region Characteristics $T_J = 25^{\circ}\text{C}$




Figure 3. On-Region Characteristics $T_J = 175^{\circ}\text{C}$




Figure 4. Normalized On-Resistance Characteristics vs. Temperature




Figure 5. Transfer Characteristics





Figure 6. Diode Forward Voltage Characteristics vs. Source-Drain Current $T_J = -40^{\circ}\text{C}$



Typical Performance Characteristics

Figure 7. Diode Forward Voltage Characteristics
vs. Source-Drain Current $T_J = 25^{\circ}\text{C}$




Figure 8. Diode Forward Voltage Characteristics
vs. Source-Drain Current $T_J = 175^{\circ}\text{C}$




Figure 9. Threshold Voltage vs. Temperature




Figure 10. Gate Charge Characteristics




Figure 11. Stored Energy in Output Capacitance





Figure 12. Capacitance Characteristics



Typical Performance Characteristics

Figure 13. Continuous Drain Current Derating vs. Case Temperature




Figure 14. Maximum Power Dissipation Derating vs. Case Temperature




Figure 15. Typ. Switching Losses vs. Drain Current




Figure 16. Typ. Switching Losses vs. Gate Resistance




Figure 17. Typ. Switching Losses vs. Drain Current





Figure 18. Typ. Switching Losses vs. Gate Resistance



Typical Performance Characteristics

Figure 19. Maximum Safe Operating Area




Figure 20. Transient Thermal Response Curve




Figure 21. Inductive Load Switching Test Circuit and Waveforms






Figure 22. Peak Diode Recovery dv/dt Test Circuit and Waveforms



Package Outlines

QDPAK



SYMBOL	MIN	MAX	SYMBOL	MIN	MAX
A	2.25	2.35	E9	0.75	
A1	0.00	0.15	e	1.14	
A2	0.90		e1	11.4	
A3	0.50		F	7.40	7.60
b	0.50	0.70	F1	1.47	1.67
b1	-	0.15	F2	7.40	7.60
c	0.46	0.58	F3	3.65	3.85
D	14.90	15.10	F4	5.07	5.27
D1	12.00		F5	10.24	10.44
D2	13.20		L	1.30	
D3	14.50	14.70	M	0.60	
E	20.81	21.11	N	22	
E1	15.30	15.50	O	0°	8°
E2	9.83		P	0.90	
E3	0.625		P1	0.70	0.90
E4	0.45		P2	0.90	1.10
E5	0.95		Q	1.60	
E6	2.53		R	1.70	
E7	2.40		S	0.631	
E8	0.90				

*Dimensions in millimeters

Package Marking and Ordering Information

Part Number	Top Marking	Package	Packing Method	Quantity
BCQ120N16M1	BCQ120N16M1	QDPAK	Tape & Reel	750 units

Disclaimer

Bestirpower reserve the right to make changes, corrections, enhancements, modifications, and improvements to Bestirpower products and/or to this document at any time without notice.

The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. Bestirpower does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.

This document is the property of Bestirpower Co.,. LTD., and not allowed to copy or transformed to other format if not under the authority approval.

© 2026 bestirpower – All rights Reserved