






ELECTRICAL
RATING:DC12V 3A:
CONTACT RESISTANCE:30mΩ MAX(INITIAL)
100mΩ MAX(FINAL)
INSULATION RESISTANCE: 100 MΩ MIN.
DIELECTRIC WITHSTAND VOLTAGE: 500V AC
DURABILITY TEST: 5,000 CYCLES.
TEMPERATURE RANGE: -25°C TO +75°C
MATERIALS & PLATING: SEE THE TABLE BELOW.
PACKAGING: TAPE&REEL



PCB LAYOUT
TOP VIEW (Tolerance:±0.05)

环保
Green Product

6	SHELL	1	SUS t=0.25mm	Ni Plated
5	9#-DETECT	1	C5191 t=0.4mm	GOLD FLASH ON CONTACT AREA 1u" MATT TIN 60u" ON SOLDER, ALL OVER 50u" NI.
4	8#-GROUND	1	C5191 t=0.2mm	
3	7#-GROUND	1	C5191 t=0.2mm	
2	5#-POWER	1	C5191 t=0.25mm	
1	HOUSING	1	PA9T UL94V-0	BLACK
NO.	PART NAME	QTY	MATERIAL	REMARK

							ANGLE	±2°	Designed:	Checked:	Approved:	Date:	MODEL TYPE:
							30 ~	±0.50				2017/04/21	DC POWER JACK
							10 ~ 30	±0.35					PART NO.
							~ 10	±0.25					CAX-DC-106-0.7-3A-XL
ECN NO	REV	DATE	DESCRIPTION	CHANGE	CHECK	APPRO.	UNSPECIFIED TOLERANCE						

浙江创都电子科技有限公司

UNIT:	SCALE:	VIEW:	Edition:
mm	1:1	⊙ ⊞	A/0