








WITH COVER



CIRCUIT*1 IDENTIFIED
ON THIS SURFACE
(APPROX. LOCATION
SHOWN FOR REF.)




Specifications:

Contact resistance: $\leq 10\text{m}\Omega$
Insulation resistance: $\geq 1000\text{M}\Omega$
Rated voltage: 250V AC DC
Rated current: 5.0A AC DC
Withstand Voltage: 1000V AC/minute
Temperature Range: $-40^\circ\text{C} \sim +125^\circ\text{C}$
Housing: LCP UL94V-0, BLACK
Contacts: Brass/MATTE Sn-plated
Solder Tabs: Brass/MATTE Sn-plated

ORDER INFORMATION:

A3007V-2XXP-F9KB3-R-X			
PART No.			SPECIAL CODE: X=Cap
No.OF CIRCUITS:			PACKAGING: R=REEL
02-24			Metal code: 3=Brass
PLASTIC MATERIAL:			PLATING: B=MATTE Sn
F9K=LCP			

浙江创都电子科技有限公司				TITLE:MX3.0双排立贴	
GENERAL TOLERANCE		USE: CUSTOMER		PART NO.:	
X. ±0.50	X. ±5°	APPD:			
X.X ±0.30	X.X ±2°			DWG NO.:	
X.XX ±0.20	X.XX ±1°	CHKD:		CAX-MX3.0-S0**LA-XT	
		UNITS: mm		DR:	
				SCALE	
				1 : 1	SHEET
					1 / 1