





REV.	ECN NO.	MODIFIED MARK	APPROVED
A	————	FIRST RELEASE	




PCB LAYOUT
TOP VIEW

COLOR TABLE

CODE	A	B	C
COLOR	WHITE	WHITE	WHITE
CODE	D	E	F
COLOR	RED	RED	RED



SCHEMATIC



NOTES:
ELECTRICAL:
1:RATED CURRENT: 0.2A Max.
2:RATED VOLTAGE: 50V AC.
3:CONTACT RESISTANCE: 30 MILLIOHMS Max.
AFTER TESTING:100 MILLIOHMS Max.
4:INSULATION RESISTANCE: 100 MEGAOHMS Min.
5:DIELECTRIC WITHSTANDING VOLTAGE: 500 VAC Min.
MECHANICAL:
1:INSERTION FORCE: 3N-30N.
2:WITHDRAWAL FORCE: 3N-30N.
3:DURRABILITY: 100 CYCLES.
ENVIRONMENTAL:
TEMPERATURE RANGE: -25°C TO 85°C.
MARK “▼” AS THE KEY CONTROL SIZE.
PIN PIN POSITION SIZE IS SUBJECT TO PCB BOARD.

⑥	TERMINAL-C	3	BRASS t=0.4	CuSn PLATED	RoHS 2.0		
⑤	TERMINAL-B	3	BRASS t=0.4	CuSn PLATED			
④	TERMINAL-A	3	BRASS t=0.4	CuSn PLATED			
③	SOCKET	6	BRASS t=0.36	CuSn PLATED			
②	WASHER	6	PBT	SEE COLOR TABLE			
①	HOUSE	1	PB	BLACK			
NO.	PART NAME	Q'TY	MATERIAL	FINISH/COLOR	REMARK		
ANGLE		±5°	MODEL NAME: (PART NO.)		浙江创都电子科技有限公司		
63 < L		±0.5					
16 < L ≤ 63		±0.4	TITLE: RCA PIN JACK				
4 < L ≤ 16		±0.3					
L ≤ 4		±0.2	REV.: A				
TOL TABLE:							
		MAT'L:	DESIGN:	09/03'25	DWG NO.: CAX-AV-607-WR-HP	REV.: A	
		See table	FINISH:	09/03'25			
		See table	CHECKED:	09/03'25	SCALE: 5:1	SHEET: 1/1	SIZE: A3
		Q'TY:/	APPROVED:	09/03'25			
			UNIT: mm	VIEW: 			