














DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyconn Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED					
.X±0.30	X.*±10°	APR.	Alex	TITLE: USB CF 24P SMT TYPE TOP-MOUNT CH=1.6mm	
.XX±0.20	.X.*±8°	CHK.	Jack	DWG NO. TYPE-C-G20-1TDL820	
.XXX±0.10	.XX.*±5°	DRA.	Can	CUSTOMER DRAWING	
SIZE A4	SCALE 1:1	SHEET 1/1	REV. A		



SCALE 2:1




RECOMMENDED PCB LAYOUT(TOP VIEW)
Thickness 1.0mm (TOLERANCE=±0.05mm)

- NOTE:
- 1.MATERIAL SPECIFICATION:
 - 1.HOUSING:HIGH TEMPERATURE RESISTANT PLASTIC,UL94 V-0(LCP,BLACK)
 - 2.TERMINAL:COPPER ALLOY(C18150)
 - 3.MID PLATE: STAINLESS STEEL(SUS301)
 - 4.OUT SHELL: STAINLESS STEEL(SUS304)
 - 5.INNER SHELL: STAINLESS STEEL(SUS304)
 - 2.PLATING SPECIFICATION:
 - 2-1.CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au 3u" PLATED ON CONTACT AREA.
Au 1u" PLATED ON SOLDER AREA.
 - 2-2.OUT SHELL&INNER SHELL:
Ni 30u" MIN. UNDER PLATED OVER ALL.
 - 2-3.MID PLATE:
Ni 30u" MIN. UNDER PLATED OVER ALL.
 - 3.MECHANICAL PERFORMANCE,
 - 3-1.INSERTION FORCE: 0.5~2.0kgf.
 - 3-2.REMOVAL FORCE: 0.8kgf~2.0kgf.(INITIAL)
0.6kgf~2.0kgf.(AFTER DURABILITY TEST)
 - 3-3.DURABILITY: 10000 CYCLES.
 - 4.ELECTRICAL PERFORMANCE,
 - 4-1. VOLTAGE RATING: 20V.
CURRENT RATING: 5A.
 - 4-2. LLCR:
VBUS & GND PINS AND OTHER PINS: 40ma/PIN MAX.
LLCR MAX. CHANGE OF ALL PINS: 10me.
 - 4-3.INSULATION RESISTANCE: 100Ma MIN
 - 4-4.DIELECTRIC WITHSTAND VOLTAGE,AC 100V FOR 1 MINUTE.
 5. ENVIRONMENTAL PERFORMANCE:
OPERATING TEMPERATURE: -55°C~+85°C.
 - 6.IR REFLOW:
THE PEAK TEMPERATURE ON THE BOARD SHALL
BE MAINTAINED FOR 10 SECONDS AT 260°C.

USB TYPE-C PIN ASSIGNMENTS

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TXp1	TXn1	Vbus	CC1	D+	D-	SBU1	Vbus	RXn2	RXp2	GND
GND	RXp1	RXn1	Vbus	SBU2	D-	D+	CC2	Vbus	TXn2	TXp2	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

DIMENSION in mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyeconn Electronics Co.,Ltd				
TOLERANCE UNLESS OTHERWISE SPECIFIED						
.X±0.30	X.*± 10°	APR. Alex	TITLE: USB CF 24P SMT TYPE TOP-MOUNT CH=1.6mm			
.XX±0.20	.X.*± 8°	CHK. Jack	DWG NO. TYPE-C-G20-1TDL820			
.XXX±0.10	.XX.*± 5°	DRA. Can	PROJ. 		CUSTOMER DRAWING	
		SIZE A4		SCALE 1:1	SHEET 1/1	REV. A



	REEL	CARTON
CONNECTOR (PCS)	900	9000

DIMENSION IN mm		厦门市辛译精密电子有限公司 Xiamen XinYi Xyecom Electronics Co.,Ltd			
TOLERANCE UNLESS OTHERWISE SPECIFIED		TITLE: USB CF 24P SMT TYPE TOP-MOUNT CH=1.6mm			
.X±0.30	X.*±10°	APR. Alex	DWG NO. TYPE-C-G20-1TDL820		
.XX±0.20	.X.*±8°	CHK. Jack	PROJ.  CUSTOMER DRAWING		
.XXX±0.10	.XX.*±5°	DRA. Can	SIZE A4	SCALE 1:1	SHEET 1/1 REV. A