




GLASS PASSIVATED SURFACE MOUNT BRIDGE RECTIFIERS

Features

- ◆ Glass Passivated Chip Junction
- ◆ Reverse Voltage - 100 to 1000 V
- ◆ Forward Current- 2.0 A
- ◆ Fast reverse recovery time
- ◆ Designed for Surface Mount Application

Mechanical Data

Case : JEDEC ABS molded plastic body
Terminals : Solderable per MIL-STD-750, Method 2026
Polarity : Polarity symbol marking on body Mounting
Position : Any
Weight : 0.0031 ounce, 0.088 grams



Dimensions in inches and (millimeters)

Maximum Ratings And Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	Symbols	RABS210	Units
Marking Code			
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	1000	V
Maximum RMS voltage	V_{RMS}	700	V
Maximum DC Blocking Voltage	V_{DC}	1000	V
Average Rectified Output Current at $T_c = 115^\circ\text{C}$	I_O	2.0	A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load (JEDEC Method)	I_{FSM}	55	A
Maximum Forward Voltage at 2.0 A	V_F	1.1	V
Maximum DC Reverse Current @ $T_a = 25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_a = 125^\circ\text{C}$	I_R	5.0 100	μA
Typical Junction Capacitance (Note 1)	C_j	40	pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	50	$^\circ\text{C/W}$
Maximum Reverse Recovery Time (Note 3)	t_{rr}	500	ns
Operating and Storage Temperature Range	T_j, T_{stg}	-55 ~ +175	$^\circ\text{C}$

Note: 1. Measured at 1MHz and applied reverse voltage of 4 V D.C.

2. Mounted on glass epoxy PC board with $4 \times 1.5 \times 1.5$ (3.81 x 3.81 cm) copper pad areas.

3. Measured with $I = 0.5 \text{ A}$, $I = 1 \text{ A}$, $I_{rr} = 0.25 \text{ A}$.



Typical Characteristics

Fig.1 Average Rectified Output Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Instantaneous Forward Characteristics




Fig.4 Typical Junction Capacitance





Fig.5 Maximum Non-Repetitive Peak Forward Surge Current



The curve above is for reference only.