






		D		E	
REV.	DESCRIPTION	ECN NO.	NAME	DATE	



USB TYPE-C PIN ASSIGNMENTS


PIN	NUMBER	SIGNAL NAME	PIN	NUMBER	SIGNAL NAME
	A1	GND		B12	GND
	A2	TXp1+		B11	RXp1+
	A3	TXn1-		B10	RXn1-
	A4	V _{bus}		B9	V _{bus}
	A5	CC1		B8	SBU2
	A6	Dp1		B7	Dn2
	A7	Dn1		B6	Dp2
	A8	SBU1		B5	CC2
	A9	V _{bus}		B4	V _{bus}
	A10	RXn2-		B3	TXn2-
	A11	RXp2+		B2	TXp2+
	A12	GND		B1	GND



RECOMMENDED P.C.B. LAYOUT (T=1.00mm)
TOLERANCE UNSPECIFIED $\pm 0.05\text{mm}$

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD				BXCONN [®]	
DIM. TOL. .x ±0.30 .xx ±0.20 .xxx ±0.10 GENERAL ANGLE: x° ±10° x.x° ±8° x.xx° ±5°		TITLE: USB C F 24PIN DIP+SMT WITH SPRING&POST					
		DWG. NO.: UC22-8B24F00P11		CHECKED: MAX			
		PART NO.: UC22-8B24F00P11		DRAWN: ELLA			
		UNIT: mm	SCALE: none	SHEET: 2 of 3	DWG. SIZE: A4	LAYER: bxconn	APPROVED: WILL





REV.	DESCRIPTION	ECN NO.	NAME	DATE

		REEL/TRAY	CARTON
CONNECTOR (PCS)		1000	10000
GENERAL TOLERANCE	DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD		
DIM.	TOL.	TITLE: USB C F 24PIN DIP+SMT WITH SPRING&POST	
.x	±0.30		
.xx	±0.20		
.xxx	±0.10		
GENERAL ANGLE:			
x.°	±10°	DWG. NO.: UC22-8B24F00P11	CHECKED: MAX
x.x°	±8°	PART NO.: UC22-8B24F00P11	DRAWN: ELLA
x.xx°	±5°	UNIT: mm	APPROVED: WILL
SCALE: none		SHEET: 3 of 3	DWG. SIZE: A4
LAYER: bxconn		APPROVED: WILL	

