

1

WWW.BXCONN.COM 东莞市宝讯精密技术有限公司 ARTICLE: BX-CN-001-A

A		B		C		D		E	
				REV.	DESCRIPTION		ECN NO.	NAME	DATE


1

2

3


4

5




USB TYPE-C PIN ASSIGNMENTS

PIN NUMBER	SIGNAL NAME	PIN NUMBER	SIGNAL NAME
A1	GND	B12	GND
A4	VBUS	B9	VBUS
A5	CC1	B8	SBU2
A6	Dp1	B7	Dn2
A7	Dn1	B6	Dp2
A8	SBU1	B5	CC2
A9	VBUS	B4	VBUS
A12	GND	B1	GND



RECOMMENDED PCB LAYOUT(TOP VIEW)
THICKNESS 0.80MM;DEFAULT TOLERANCE:±0.05

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN [®]	
DIM.	TOL.	TITLE: USB CF 16PIN (L=6.5) MID MOUNT 2.1MM						
.x	±0.30	DWG. NO.: UC22-0B16FCH052					CHECKED: MAX	
.xx	±0.20							
.xxx	±0.10	PART NO.: UC22-0B16FCH052					DRAWN: ELLA	
GENERAL ANGLE:								
.x°	±8°	UNIT: mm					APPROVED: WILL	
.xx°	±5°							
		SCALE: none	SHEET: 2 of 3	DWG. SIZE: A4	LAYER: bxconn			

