







RoHs

VER	MARK	PR. BY	DESCRIPTION	DATE



2Pin



PIN number variable size comparison table

PART NO	PIN	A	B	C
HMT-XH2.54-WT2P	2	2.50	10.00	8.30
HMT-XH2.54-WT3P	3	5.00	12.50	10.80
HMT-XH2.54-WT4P	4	7.50	15.00	13.30
HMT-XH2.54-WT5P	5	10.00	17.50	15.80
HMT-XH2.54-WT6P	6	12.50	20.00	18.30
HMT-XH2.54-WT7P	7	15.00	22.50	20.80
HMT-XH2.54-WT8P	8	17.50	25.00	23.30
.....				
HMT-XH2.54-WT16P	16	37.50	45.00	43.30

NOTES:

1. BASE: LCP
2. PIN: Brass
3. Solder Tab: Brass

SPECIFICATIONS:

1. Spacing: 2.5
2. Voltage Rating: 250V AC DC
3. Current Rating: 3A AC DC
4. Insulation Resistance: 800MΩ Min
5. Contact Resistance: 20mΩ Max
6. Withstanding voltage: 1000V AC 1/Minute
7. Temperature Range: -25℃ ~+ 85℃

GENERAL TOLERANCES
UNLESS SPECIFIED

X.X ±0.30	X.° ±5°
.XX ±0.20	X.X° ±1°
.XXX ±0.10	X.XX° ±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-XH2.54-WTNP

DESIGN: James

CHED: Talen

APPD: Sophia

TITLE:
WAFER 2.54 卧贴

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1