






RoHs

General tolerances(mm)

$0_{\sim}$	$>3_{\sim}$	$>6_{\sim}$	$>10_{\sim}$	$>18_{\sim}$	$>30_{\sim}$	$>50_{\sim}$	$>80_{\sim}$	$>120_{\sim}$	$>180_{\sim}$	$>250_{\sim}$	$>315_{\sim}$	$>400_{\sim}$	>500	$0.1/10$
3	6	10	18	30	50	80	120	180	250	315	400	500		$\angle$
± 0.12	± 0.18	± 0.22	± 0.26	± 0.31	± 0.37	± 0.57	± 0.80	± 0.93	± 1.05	± 1.15	± 1.60	± 2.20	± 2.50	$\pm 2^{\circ}$



PCB LAYOUT

Product model	PIN	A	B	C
HMT-EDGRC-5.08-1-2PMG	2	12.16	5.08	5.08
HMT-EDGRC-5.08-1-3PMG	3	17.24	10.16	10.16
HMT-EDGRC-5.08-1-4PMG	4	22.32	15.24	15.24
HMT-EDGRC-5.08-1-5PMG	5	27.40	20.32	20.32
HMT-EDGRC-5.08-1-6PMG	6	32.48	25.40	25.40
HMT-EDGRC-5.08-1-7PMG	7	37.56	30.48	30.48
.....				
HMT-EDGRC-5.08-1-24PMG	24	5.08xN+2	5.08x(N-1)	5.08x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	III/3	III/2	II/2
Rated Voltage(V)/Current(A)	/	320/20	/
Rate Impulse Voltage(KV)	/	4	/
Pitch(mm)/Poles	5.08/N=02~24P		
Operating temperature(°C)	-40~+105		
Conform to RoHS	Yes		

2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCES
UNLESS SPECIFIED

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.		TITLE:		
HMT-EDGRC-5.08-1-NPMG		Socket-type terminal		
DESIGN:	James	CUSTOMER	SIZE	UNITS
			A4	MM
CHED:	Talen		SCALE	SHEET
APPD:	Sophia		N:A	1/1