




RoHs

2.00 ± 0.15 (PITCH)




Technical Index:

1. Temperature range: $-25^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
2. Rated voltage: 200V DC/AC(rms).
3. Rated current: 2.0A.
4. Contact resistance: $\leq 25\text{m}\Omega$.
5. Withstanding voltage: 500V AC/minute.
6. Insulation resistance: $\geq 1000\text{M}\Omega$.




3.40 ± 0.20




SECTION A-A

Part No	Pin	A	B
HMT-PH2.0-WZR2P	2	2.00	6.00
HMT-PH2.0-WZR3P	3	4.00	8.00
HMT-PH2.0-WZR4P	4	6.00	10.00
HMT-PH2.0-WZR5P	5	8.00	12.00
HMT-PH2.0-WZR6P	6	10.00	14.00
HMT-PH2.0-WZR7P	7	12.00	16.00
HMT-PH2.0-WZR8P	8	14.00	18.00
HMT-PH2.0-WZR9P	9	16.00	20.00
HMT-PH2.0-WZR10P	10	18.00	22.00
HMT-PH2.0-WZR11P	11	20.00	24.00
HMT-PH2.0-WZR12P	12	22.00	26.00
HMT-PH2.0-WZR13P	13	24.00	28.00
HMT-PH2.0-WZR14P	14	26.00	30.00
HMT-PH2.0-WZR15P	15	28.00	32.00
HMT-PH2.0-WZR16P	16	30.00	34.00
HMT-PH2.0-WZR17P	17	32.00	36.00
HMT-PH2.0-WZR18P	18	34.00	38.00
HMT-PH2.0-WZR19P	19	36.00	40.00
HMT-PH2.0-WZR20P	20	38.00	42.00



适用线路板 (PCB LAYOUT)

序号	品名	材质
1	PH2.0 弯针 胶芯	PA66 UL94V-2 Red
2	PH2.0 弯针 端子	Copper Alloy/ Tin Plating

GENERAL TOLERANCES UNLESS SPECIFIED		 HMT CONN 深圳市华明通电子有限公司 Shenzhen Huamingtong Electronics Co., Ltd			
X.° ±0.50	X.° ±5°	PART NO.		TITLE:	
X.X° ±0.20	X.X° ±3°	HMT-PH2.0-WZRN		PH2.0 弯针	
X.XX°±0.10	X.XX° ±1°	DESIGN: James	CUSTOMER	SIZE	UNITS
MANUFACTURE DWG		CHED: Talen		A4	MM
		APPD: Sophia		SCALE	SHEET
				N:A	1/1