

HBS Plastic-Encapsulate Bridge Rectifier

Features

- Ideal for printed circuit board
- Glass passivated junction
- High surge current capability
- The plastic material used carries Underwriters Laboratory flammability recognition 94V-0
- High temperature soldering guaranteed: 260/10 seconds at 5lbs., (2.3kg) tension



Applications

General purpose 1 phase Bridgerectifier applications


Mechanical Data

- Case: HBS
Molding compound meets UL 94V-0 flammability rating, RoHS-compliant, halogen-free
- Terminals: Solder plated, solderable per MIL-STD-750,Method 2026
- Polarity: Polarity symbols molded or Marked on body

Function Diagram



Reverse Voltage
1000 V
Forward Current
4.0 Ampere







Maximum Ratings (Ta=25°C Unless otherwise specified)

PARAMETER	SYMBOL	UNIT	RHBS410
Device marking code			RHBS410
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	V	1000
Maximum RMS Voltage	V_{RMS}	V	700
Maximum DC blocking Voltage	V_{DC}	V	1000
Maximum Average Forward Rectified Current @60Hz sinewave, Resistance load,TL (Fig.1)	$I_{F(AV)}$	A	4
Non-repetitive Peak Forward Surge Current @ t=8.3ms Half-sine wave	I_{FSM}	A	120
Rating for fusing (t=8.3ms, Ta=25 °C)	I^2t	A ² S	59.76
Storage temperature	T_{stg}	°C	-55 ~+150
Junction temperature	T_j	°C	-55 ~+150
Typical Thermal Resistance	$R_{\theta J-A}$	°C /W	40
	$R_{\theta J-C}$		14
	$R_{\theta J-L}$		20

● **Electrical Characteristics** (Ta=25°C Unless otherwise noted)

PARAMETER	TEST CONDITIONS	SYMBOL	UNIT	RHBS410
Maximum instantaneous forward voltage	$I_F=4.0A$	V_F	V	1.3
Maximum DC reverse currentat rated DC blocking voltage	$V_R=V_{DC}, T_A=25^{\circ}C$	I_{R1}	μA	5
	$V_R=V_{DC}, T_A=125^{\circ}C$	I_{R2}		100
Maximum reverse recovery time	$I_F=0.5A, I_R=1.0A, I_{RR}=0.25A$	T_{rr}	ns	350

● **Ratings And Characteristics Curves** (Ta=25°C Unless otherwise specified)



● Ordering Information

PACKAGE	PACKAGE CODE	REEL(pcs)	BOX(pcs)	CARTON(pcs)	DELIVERY MODE
HBS	R3	2500	5000	20000	13"

● Package Outline Dimensions (HBS)

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	1.30	1.90	0.051	0.075
A1	0.05	0.20	0.002	0.008
B	9.90	10.50	0.390	0.413
C	0.15	0.35	0.006	0.014
D	6.90	7.50	0.272	0.295
E	9.70	10.30	0.382	0.406
b	1.30	1.70	0.051	0.067
e	4.80	5.50	0.189	0.217

● Suggested Pad Layout

Symbol	Dimensions			
	Millimeters		Inches	
	Min.	Max.	Min.	Max.
M	9.30	—	0.366	—
N	3.50	—	0.138	—
Y	1.00	—	0.039	—
X	1.60	—	0.063	—