




Features

- Available Output Voltage:12V
- Maximum Input Voltage: 35V
- Maximum Output Current:
Exceed 500mA at $T_J = 25^{\circ}\text{C}$
- Output Tolerances:
 $\pm 3\%$ at $T_J = 25^{\circ}\text{C}$
 $\pm 5\%$ over the Operating T_J
- No External Components

Applications


- Motor Drives
- On-Card Regulation
- Portable Devices
- Telecommunications
- TVs and Set-top Boxes



Ordering Information

Product ID	Pack	Marking	Qty(PCS)
L7805CDT	TO-252-2L	78M05	2500

Typical Application Circuit





Absolute Maximum Ratings

CHARACTERISTIC	SYMBOL	VALUE	UNIT
Maximum input voltage	V_{IN}	35	V
Maximum junction temperature	$T_{J Max}$	150	°C
Storage temperature	T_{stg}	- 65 ~ 150	°C
Soldering temperature & time	T_{solder}	260°C, 10s	-

Electrical Characteristics

78M12 ($V_{IN} = 19V$, $I_{OUT} = 350mA$, $C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1\mu F$, $T_J = 25^\circ C$, unless otherwise specified)

CHARACTERISTIC	SYMBOL	TEST CONDITIONS ⁽¹⁾	MIN.	TYP. ⁽²⁾	MAX.	UNIT
Output voltage ⁽³⁾	V_{OUT}	-	11.64	12.00	12.36	V
		$V_{IN} = 14.5$ to $27V$, $I_{OUT} = 5$ to $350mA$	11.40	12.00	12.60	
Line regulation	LNR	$V_{IN} = 14.5$ to $30V$, $I_{OUT} = 200mA$	-	10	100	mV
		$V_{IN} = 16$ to $30V$, $I_{OUT} = 200mA$	-	3.0	50	
Load regulation	LDR	$I_{OUT} = 5$ to $500mA$	-	25	240	mV
		$I_{OUT} = 5$ to $200mA$	-	10	120	
Quiescent current	I_Q	-	-	4.6	6.0	mA
Quiescent current change	ΔI_Q	$V_{IN} = 14.5$ to $30V$, $I_{OUT} = 200mA$	-	-	0.8	mA
		$I_{OUT} = 5$ to $350mA$	-	-	0.5	
Output noise voltage	V_N	$f = 10$ to $100kHz$	-	75	-	μV
Ripple rejection	RR	$V_{IN} = 15$ to $25V$, $I_{OUT} = 300mA$, $f = 120Hz$	55	80	-	dB
Dropout voltage ⁽⁴⁾	V_D	$I_{OUT} = 350mA$	-	2.0	-	V
Short circuit current	I_{SC}	$V_{IN} = 19V$, OUT short to GND	-	240	-	mA
Peak current	I_{Peak}	-	-	0.7	-	A

Note:

(1) Pulse test technology is used to make T_J as close to T_A as possible. Thermal effects must be considered separately.

(2) Typical numbers are at $25^\circ C$ (T_J) and represent the most likely norm.







(3) This specification only applies to the DC power consumption allowed by the absolute maximum rating.

(4) The difference of output voltage and input voltage when input voltage is decreased gradually till output voltage equals to 95% of V_{OUT} .



Typical Characteristics

($C_{IN} = 0.33\mu F$, $C_{OUT} = 0.1\mu F$, $T_J = 25^\circ C$, unless otherwise specified)





Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.