




Description

The IPD90P03P404ATMA1 uses advanced trench technology to provide excellent $R_{DS(ON)}$, low gate charge and operation with gate voltages as low as 4.5V. This device is suitable for use as a Battery protection or in other Switching application.




TO-252-2L

General Features

$V_{DS} = -30V$ $I_D = -100A$

$R_{DS(ON)} < 4.5m\Omega$ @ $V_{GS} = -10V$



P-Channel MOSFET

Application

Lithium battery protection

Wireless impact

Mobile phone fast charging

Ordering Information

Product ID	Pack	Brand	Qty(PCS)
IPD90P03P404ATMA1	TO-252-2L	HXY MOSFET	2500

Absolute Maximum Ratings (TC=25°C unless otherwise noted)

Symbol	Parameter	Max.	Units
VDSS	Drain-Source Voltage	-30	V
VGSS	Gate-Source Voltage	±20	V
ID	Continuous Drain Current $T_C = 25^\circ C$	-100	A
ID	Continuous Drain Current $T_C = 100^\circ C$	-59	A
IDM	Pulsed Drain Current ^{note1}	-360	A
EAS	Single Pulsed Avalanche Energy ^{note2}	210	mJ
PD	Power Dissipation $T_C = 25^\circ C$	109	W
RθJC	Thermal Resistance, Junction to Case	1.4	°C/W
TJ, TSTG	Operating and Storage Temperature Range	-55 to +175	°C



Electrical Characteristics@T_J=25°C(unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
V(BR)DSS	Drain-Source Breakdown Voltage	VGS=0V, ID= -250μA	-30	-33	-	V
IDSS	Zero Gate Voltage Drain Current	VDS= -30V, VGS=0V,	-	-	-1	μA
IGSS	Gate to Body Leakage Current	VDS=0V, VGS= ±20V	-	-	±100	nA
VGS(th)	Gate Threshold Voltage	VDS=VGS, ID= -250μA	-1.0	-1.6	-2.5	V
RDS(on)	Static Drain-Source on-Resistance	VGS= -10V, ID= -30A	-	3.5	4.5	mΩ
		VGS= -4.5V, ID= -20A	-	4.8	6.2	
Ciss	Input Capacitance	VDS= -15V, VGS=0V, f=1.0MHz	-	6800	-	pF
Coss	Output Capacitance		-	769	-	pF
Crss	Reverse Transfer Capacitance		-	726	-	pF
Qg	Total Gate Charge	VDS= -15V, ID= -30A, VGS= -10V	-	30	-	nC
Qgs	Gate-Source Charge		-	6	-	nC
Qgd	Gate-Drain("Miller") Charge		-	8	-	nC
td(on)	Turn-on Delay Time	VDD= -15V, ID= -30A, VGS= -10V, RGEN=2.5Ω	-	11	-	ns
tr	Turn-on Rise Time		-	13	-	ns
td(off)	Turn-off Delay Time		-	52	-	ns
tf	Turn-off Fall Time		-	21	-	ns
IS	Maximum Continuous Drain to Source Diode Forward Current		-	-	-100	A
ISM	Maximum Pulsed Drain to Source Diode Forward Current		-	-	-360	A
VSD	Drain to Source Diode Forward Voltage	VGS=0V, IS= -30 A		-0.8	-1.2	V

Notes:

- 1、Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature
- 2、EAS condition: T_J =25°C, V_{DD} = -15V, V_G = -10V, R_G =25Ω, L=0.5mH, I_{AS} = -29A
- 3、Pulse Test: Pulse Width≤300μs, Duty Cycle≤2%



Typical Characteristics




Figure1: Output Characteristics




Figure 2: Typical Transfer Characteristics




Figure 3: On-resistance vs. Drain Current




Figure 4: Body Diode Characteristics




Figure 5: Gate Charge Characteristics




Figure 6: Capacitance Characteristics




Figure 7: Normalized Breakdown Voltage vs. Junction Temperature




Figure 8: Normalized on Resistance vs. Junction Temperature




Figure 9: Maximum Safe Operating Area




Figure 10: Maximum Continuous Drain Current vs. Case Temperature





Figure.11: Maximum Effective Transient Thermal Impedance, Junction-to-Case



TO-252-2L Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 TYP.		0.190 TYP.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 TYP.		0.114 TYP.	
L2	1.400	1.700	0.055	0.067
L3	1.600 TYP.		0.063 TYP.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 TYP.		0.211 TYP.	



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.