

RoHs





VER	MARK	PR. BY	DESCRIPTION	DATE

NOTES:


1. BASE: LCP
2. PIN: Brass
3. Solder Tab: Brass

SPECIFICATIONS:

1. Spacing: 2.0
2. Voltage Rating: 250V AC DC
3. Current Rating: 2A AC DC
4. Insulation Resistance: 800M Ω Min
5. Contact Resistance: 20m Ω Max
6. Withstanding voltage: 500V AC 1/Minute
7. Temperatuer Range: -25 $^{\circ}$ C ~+ 85 $^{\circ}$ C



PIN number variable size comparison table				
PART NO	Pin	A	B	C
HMT-PH2.0-WT2P	2	2.00	8.00	6.80
HMT-PH2.0-WT3P	3	4.00	10.00	8.80
HMT-PH2.0-WT4P	4	6.00	12.00	10.80
HMT-PH2.0-WT5P	5	8.00	14.00	12.80
HMT-PH2.0-WT6P	6	10.00	16.00	14.80
HMT-PH2.0-WT7P	7	12.00	18.00	16.80
.....				
HMT-PH2.0-WT16P	16	30.00	36.00	34.80



GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X. $^{\circ}$	±5 $^{\circ}$
.XX	±0.20	X.X $^{\circ}$	±1 $^{\circ}$
.XXX	±0.10	X.XX $^{\circ}$	±0.5 $^{\circ}$

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-PH2.0-WTNP

DESIGN: James
CHED: Talen
APPD: Sophia

TITLE:
WAFER 2.00 贴片

CUSTOMER	SIZE	UNITS
	A4	MM
	SCALE	SHEET
	N:A	1/1