

MESSRS.

SPECIFICATION FOR APPROVAL**承 認 书**

Product	MAGNETIC BUZZER (INDICATOR)
Part No.	HX-1205-P28N (RoHS)
Customer Approval	

Approved By	Checked By	Made By
王台平 JAN-10-2022	曹丽萍 JAN-10-2022	LILY JAN-10-2022

常 州 华 龙 电 子 有 限 公 司**DRAGONSTATE ELECTRONIC CORPORATION**

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

EDITION:1.1

1. Specifications

HX-1205-P28N (RoHS)

Items		Units	Specifications	Conditions
01	Rated Voltage	VDC	5	Response Time 500 mSec
02	Operating Voltage	VDC	3 ~ 7	Volts D.C
03	Consumption Current	mA (Max)	Mean 30	Applying rated voltage
			Peak 90	
04	Direct Current Resistance	Ohm	None	
05	Sound Output	dBA (min)	85	Distance at 10cm, applying rated voltage
06	Basic Frequency	Hz	2700± 300	
07	Operating Temp.	°C	-40 ~ +85	
08	Storage Temp.	°C	-40 ~ +85	
09	Weight	Gram	2.0	

2. Measuring Method

2-1. Test Condition

STANDARD

Temperature : 15 ~ 35°C

Relative humidity : 25% ~ 85%,

Atmospheric pressure : 860mbar to 1060mbar.


JUDGEMENT

Temperature : 20±3°C



Relative humidity : 60% ~ 70%,

Atmospheric pressure : 860mbar to 1060mbar


2-3. Standard Test Fixture



2-4. Frequency Response Curve





REV NO.	REVISION NOTE	APPROVAL	DATE
---------	---------------	----------	------



TITLE: SOUND TRANSDUCER DIMENSIONS		DRAWN: Lily	2021/07/21	SCALE: 3/1	SHEET: 1 OF 1
PART NO. HX-1205-P28N	1	DESIGNED: R&D OF D.S.	UNITS: mm		
DWG NO. DTE-5076		CHECKED: Emily	TOLERANCE ± 0.5		
		APPROVAL: Eric	UNLESS OTHERWISE SPECIFIED:		
	REV	MATERIAL: PBT	ONE PLACE DECIMAL ± ***		
			TWO PLACE DECIMAL ± ***		
			THREE PLACE DECIMAL ± ***		






DRAGONSTATE ELECTRONIC CORPORATION

Item		Test conditions	Evaluation standard
01	High temp. Storage life	The part shall be capable of withstanding a storage Temperature of 85°C for 96 hours.	After the test the part shall meet specifications without Any degradation in appearance and performance except S.P.L S.P.L shall be 73dB or more.
02	Low temp. Storage life	The part shall be capable of withstanding a storage Temperature of -40°C for 96 hours.	
03	Temp. cycle	The part shall be subjected 10 cycles. One cycle shall consist of; 	
04	Temp./Humidity cycle	The part shall be subjected 10 cycles. One cycle shall be 12 hours and consist of; 	
05	Operating life	Rated Voltage applied. - Ordinary temperature The part shall be subjected to 240 hours at room temperature (25 ±10°C) - High temperature The part shall be subjected to 500 hours at 85°C - Low temperature The part shall be subjected to 500 hours at -40°C	
06	Lead Strength	Pull load on the direction of the lead axis for 10 ±1 sec.	
07	Vibration	The part shall be subjected to a vibration cycle of 10Hz to 55Hz to 10Hz in a period of 1 minute. Total peak amplitude shall be 1.52mm (9.3G). The vibration test shall consist of 2 hours per plane in each three mutually perpendicular planes for a total time of 6 hours.	

Item		Test conditions	Evaluation standard
08	Fixed drop	The part shall be mounted on standard pc board and dropped from a height of 152cm onto a concrete floor 5 times in each 6 planes.(a total of 30 times)	After the test the part shall meet specifications without Any degradation in appearance and performance except S.P.L S.P.L shall be 74dB or more.
09	Free drop	The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total of 9 times).	
10	Solder heat resistance	Soldering into solder bath : $350\pm 5^{\circ}\text{C}$ Soaking time : 3.5 ± 0.5 sec	
11	Solder ability	Soldering : $260\pm 5^{\circ}\text{C}$ / 10 Sec. $350\pm 5^{\circ}\text{C}$ / 1.5 Sec Soldering t into solder bath : $260\pm 5^{\circ}\text{C}$ / 2 ± 0.5 sec.	
12	Lead strength	Pull lead with a force of 10N,on the direction of the lead axis for 10 : 10 ± 1 sec	
13	Wash ability	Solvent : demonized water Solvent temp. : $55\pm 5^{\circ}\text{C}$ Soaking time : 5 ± 0.5 min.	

5.Packing

REV NO.	REVISION NOTE	APPROVAL	DATE
1 FLAT = 100 PCS. 10 FLAT = 1 SAMALL BOX  x10  PLASTIC BAG 44*43 5 SMALL BOX = 1 BIG BOX Gross Weight :10Kgw. Net Weight :11.5Kgw. MADE IN CHINA 			
TITLE: PACKING		DRAWN: Lily	2013/05/29
PART NO.		DESIGNED: R&D OF D.S.	SCALE: SHEET:
DWG NO.		CHECKED: Emily	UNITS: cm
		APPROVAL: Eric	TOLERANCE ±0.1
		UNLESS OTHERWISE SPECIFIED: ONE PLACE DECIMAL ± *** TWO PLACE DECIMAL ± *** THREE PLACE DECIMAL ± ***	
REV 1		MATERIAL: *****	
DS DRAGONSTATE ELECTRONIC CORPORATION			