





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

NOTE:
1.MATERIAL:
1.1 INSULATOR:HIGH TEMPERATURE PLASTIC LCP BLACK ROHS
1.2 CONTACT:H62
1.3 SHELL:SPCC
2.ELECTRICAL CHARACTERISTICS;
2.1 CONTACTRESISTANCE:30mΩ MAX
2.2 CONTACT CURRENT RATING:1.5A
2.3 DIELECTRIC WITHSTANDING VOLTAGE:100 V R.M.S.
2.4 INSULATION RESISTANCE 100 MΩ MIN
2.5 OPERATING TEMPERATURE:-25°C ~ 85°C
3 MECHANICAL CHARACTERISTICS:
3.1 MATING FORCE:3.57kgf MAX
3.2 UNMATING FORCE:1.02kgf MIN
3.3 DURABILITY:MANDATORY:1,500 CYCLES
4.PLATING
4.1 TERMINAL:
50u" MIN NICKEL ALL OVER
100u"MIN Tin ON SOLDER AREA
1U"Au ON CONTACT AREA
4.2 SHELL: 50u"MIN.NICEL ALL OVER



Pin NUMBER	SIGNAL NAME
1	VBUS
2	D-
3	D+
4	GND
5	StdA_SSRX-
6	StdA_SSRX+
7	GND_DRAIN
8	StdA_SSTX-
9	StdA_SSTX+
Shell	Shield



COSTOMTER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING		TITLE		TYPE-A连接器9PIN弯插L16.7 (卷口)	REV. A
CHECK		PART NO.		LAIL-TYPE-A-9P-01-WC	UNITS mm
APPROVAL		DWG.NO.			Projection
TOLERANCES ARE					
30-150	±0.35	ANGLE			
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				