






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

产品规格说明: (specifications)
电器特性: (Electrical characteristics)
1. 接触阻抗: (Contact Resistance)
 最大值30毫欧: (30 milliohms MAX)
2. 耐电压: (Dielectnic Withstanding Voitage:)
 500 伏特交流电 (500V AC AT Sea Levol)
3. 绝缘阻抗: (Insulation Resistance:)
 最小值1000兆殴姆 (1000 mega-ohms MIN)
机械性能: (Mechanical:)
1. 插入力: (Insertion Force)
 最大3.57kg (3.57kg MAX)
2. 拔出力: (Unmating Force:)
 最少1.02kg (1.02 kg MIN)

材料:Material:
1. 塑胶: (Housing) : PBT白色
2. 端子: (Contact): T0.25黄铜
3. 外壳: (Shell) : T0.3 SPCC
电镀: (Finish):
1. 端子 (Contact): Au Plated ON Contact Area Over
 60~80U Ni, Sn Plated On Solder Tails.
2. 外壳: (Shell): Nickel Plating 镀亮镍60u''
 接触点镀金 0.5u'' 脚镀锡.



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司		
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD		
CHECK					
APPROVAL					
TOLERANCES ARE			TITLE	USB连接器Type-A 4PIN-直插L19.5(直口)	REV. A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-TYPE-A-4P-01-ZC	UNITS mm
10-30	±0.2				
5-10	±0.15		DWG.NO.		Projection
0-5	±0.1				