

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

备注:

1. 产品规格:

1.1 插入力:35N Max.

1.2 拔出力:10N MIN. INITIAL 8-20N AFTER 3000 CYCLES

1.3 额定电流:1.0A

1.4 额定电压:30V

1.5 耐久性:3000 CYCLES MIN.

1.6 耐电压:100V AC MIN.

1.7 接触阻抗:30mΩ MAX. INITIAL;40mΩ MAX AFTER 3000 CYCLES

1.8 绝缘电阻:100MΩ MIN

1.9 工作温度:-30° TO +80°





2. 材质:

2.1 胶芯: UL94V-0 LCP Black ROHS

2.2 端子: C5191 镀金G/Fu"

2.3 外壳: SUS201 镀雾锡30U"

3. 所用材质须符合RoHS要求



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	MICRO-B连接器5PIN-直插H5.0(直口)	REV.	A
30-150	±0.35	PART NO.	LAIL-MICRO-B-5P-02-ZC	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG.NO.		Projection	
±3°					