











REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK

1. SPECIFICATION
- 1.1 CURRENT RATE: 5A FOR VBUS; 1.25A FOR GND PIN, 0.25A FOR OTHER.
 - 1.2 VOLTAGE: 20VDC MAX
 - 1.3 CONTACT RESISTANCE: 40mΩ MAX. FOR VBUS , GND AND OTHER CONTACTS. 50mΩ MAX. AFTER ENVIRONMENT TEST
 - 1.4 INSULATOR RESISTANCE: 100M OHMS Min. AT 500V DC
 - 1.5 DIELECTRIC STRENGTH: 100V AC PER MINUTE
 - 1.6 MATING FORCE: 5~20N
UNMATING FORCE: 6~20N(INITIAL),
 - 1.7 DURABILITY : 10,000 MATING CYCLES.
 - 1.8 OPERATION TEMPERATURE: -55°C TO +85°C
2. NOTES:
- 2.1 ALL COMPONENTS ARE RoHS2.0 COMPLIANT.
 - 2.2 RESISTANCE TO SOLDERING HEAT: 265°C FOR 5 SECONDS, AND ONLY FOR WAVE SOLDERING PROCESS.
 - 2.3 SALT SPRAY:24HOURS






DIMENSION CLASSIFICATION			台灣碩方精密電子科技有限公司							
■ : CRITICAL			TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD							
☒ : MAJOR			TITLE	MU-333-M 組合式连接器 下层3.1TYPE-C连接器			開關, 连接器 SOFNG			
TOLERANCE TABLE										
.X	±	0.40	PART NO.	MU-333-M			SERIES	SD106		
.XX	±	0.25	APPROVED	Peck	DWG NO.		SOF-G006			
.XXX	±	0.10	CHECKED	Paul	SCALE	1:1	UNIT	mm	SIZE	A4
ANGLE	±	2°	DRAWIN	David		REV	AO	SHEET NO.	1/1	

P.C.B LAYOUT

REVISION

LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK





PACK DIRECTION

包装明细:

每盘装数300PCS

2.每箱10盘, 共计3000PCS

3.纸箱尺寸: 34X34X38CM



CONNECTOR EDGE(TOP VIEW)

HIGE RISE USB3.1+USB TYPE C

PIN	Signal NAME	NO.	PIN	Signal NAME	NO.
A 1	GND	1	B12	GND	13
A 2	SSTXp1	2	B11	SSRXp1	14
A 3	SSTXn1	3	B10	SSRXn1	15
A 4	V BUS	4	B 9	V BUS	16
A 5	CC1	5	B 8	SBU2	17
A 6	Dp1	6	B 7	Dn2	18
A 7	Dn1	7	B 6	Dp2	19
A 8	SBU1	8	B 5	CC2	20
A 9	V BUS	9	B 4	V BUS	21
A10	SSRXn2	10	B 3	SSTXn2	22
A11	SSRXp2	11	B 2	SSTXp2	23
A12	GND	12	B 1	GND	24

DIMENSION CLASSIFICATION

■ : CRITICAL

☒ : MAJOR

TOLERANCE TABLE

.X	±	0.40
.XX	±	0.25
.XXX	±	0.10
ANGLE	±	2°

台灣碩方精密電子科技有限公司
TAIWAN SOFNG PRECISION ELECTRONIC CO., LTDTITLE MU-333-M 組合式连接器
下层3.1TYPE-C连接器開關, 连接器
SOFNG

PART NO. MU-333-M

SERIES SD106

APPROVED Peck

DWG NO. SOF-G006

CHECKED Paul

SCALE 1:1 UNIT mm SIZE A4

DRAWIN David

REV AO SHEET NO. 1/1