


Product Summary

- V_{DS} 60V
- I_D 185A
- $R_{DS(ON)}$ (at $V_{GS}=10V$) $< 3.5m\Omega$
- 100% EAS Tested
- 100% ∇V_{DS} Tested




General Description

- Split gate trench MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low $R_{DS(ON)}$
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free

Applications

- Power switching application
- Uninterruptible power supply
- DC-DC convertor
- Motor drivers



ABSOLUTE MAXIMUM RATINGS ($T_J=25^\circ\text{C}$ unless otherwise noted)

Parameter	Symbol	Value	Unit
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	± 20	V
Continuous Drain Current ($T_c=25^\circ\text{C}$) ⁽¹⁾	I_D	185	A
Continuous Drain Current ($T_c=100^\circ\text{C}$)	I_D	116	A
Pulsed Drain Current ⁽¹⁾	I_{DM}	740	A
Drain Power Dissipation	P_D	104	W
Single Pulsed Avalanche Energy ⁽²⁾	E_{AS}	360	mJ
Thermal Resistance from Junction to Ambient	$R_{\theta JA}$	45	$^\circ\text{C/W}$
Junction Temperature	T_J	-55~ +150	$^\circ\text{C}$
Storage Temperature	T_{STG}	-55~ +150	$^\circ\text{C}$

Notes:

- 1) Repetitive Rating: pulse width limited by maximum junction temperature
- 2) EAS condition : $T_J=25^\circ\text{C}$, $V_{DD}=20V$, $V_G=10V$, $L=1.0mH$, $R_g=25\Omega$, $I_{AS}=26.8A$

Ordering Information



Order number	Package	Marking	Operation Temperature Range	MSL Grade	Ship, Quantity	Green
JSM035N06DGH	TO-252	035N06DGH	-55 to 150 $^\circ\text{C}$	1	T&R, 2500	Rohs

MOSFET ELECTRICAL CHARACTERISTICS(T_J=25°C unless otherwise noted)



Parameter	Symbol	Test Condition	Min	Type	Max	Unit
Static Characteristics						
Drain-source breakdown voltage	V _{(BR)DSS}	V _{GS} = 0V, I _D =250μA	60	-	-	V
Zero gate voltage drain current	I _{DSS}	V _{DS} =60V, V _{GS} = 0V	-	-	1	μA
Gate-body leakage current	I _{GSS}	V _{GS} =±20V, V _{DS} = 0V	-	-	±100	nA
Gate threshold voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =250μA	2.0	3.0	4.0	V
Drain-source on-resistance	R _{DS(on)}	V _{GS} =10V, I _D =20A	-	2.6	3.5	mΩ
Forward transconductance	R _g	V _{GS} = 0V, V _{DS} = 0V, f=1.0MHz	-	1.2	-	Ω
Dynamic characteristics						
Input Capacitance	C _{iss}	V _{DS} =30V, V _{GS} =0V, f=1MHz	-	2717	-	pF
Output Capacitance	C _{oss}		-	1089	-	
Reverse Transfer Capacitance	C _{rss}		-	48	-	
Switching characteristics						
Turn-on delay time	t _{d(on)}	V _{DD} =30V, I _D =20A, R _G =3Ω, V _{GS} =10V	-	7.2	-	nS
Turn-on rise time	t _r		-	11	-	
Turn-off delay time	t _{d(off)}		-	24	-	
Turn-off fall time	t _f		-	11	-	
Total Gate Charge	Q _g	V _{DS} =30V, I _D =20A, V _{GS} =10V	-	45	-	nC
Gate-Source Charge	Q _{gs}		-	11.6	-	
Gate-Drain Charge	Q _{gd}		-	11.5	-	
Source-Drain Diode characteristics						
Diode Forward voltage	V _{SD}	T _J =25℃, V _{GS} =0V, I _S =20A	-	0.8	1.2	V
Diode Forward current	I _S	T _C =25℃	-	-	185	A
Body Diode Reverse Recovery Time	trr	T _J =25℃, I _F =20A,di/dt=100A/us	-	43	-	nS
Body Diode Reverse Recovery Charge	Qrr		-	59	-	nC

Test Circuit & Waveform



Gate Charge Test Circuit & Waveform





Resistive Switching Test Circuit & Waveforms



Unclamped Inductive Switching (UIS) Test Circuit & Waveforms



Diode Recovery Test Circuit & Waveforms



Typical Characteristics




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Gate-Source Voltage




Figure 4: On-Resistance vs. Drain Current




Figure 5: On-Resistance vs. Junction Temperature




Figure 6: Source-Drain Diode Forward Voltage

Typical Characteristics




Figure 7: Gate Threshold Variation vs. Junction Temperature




Figure 8: Gate Charge Characteristics




Figure 9: Capacitance Characteristics




Figure 10: Power Derating




Figure 11: Current Derating




Figure 12: Safe Operating Area

Typical Characteristics





Figure 13: Normalized Maximum Transient Thermal Impedance


Package Information

TO-252-2



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.635	0.770	0.025	0.030
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	4.830 REF.		0.190 REF.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.712	10.312	0.382	0.406
L1	2.900 REF.		0.114 REF.	
L2	1.400	1.700	0.055	0.067
L3	1.600 REF.		0.063 REF.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.250 REF.		0.207 REF.	

TO-252-2L Suggested Pad Layout



Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$.
3. The pad layout is for reference purposes only.

Revision History

Rev.	Change	Date
V1.0	Initial version	8/21/2021

Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsemsemi.com or visit www.jsemsemi.com