

## Product Summary



- $V_{DS}$  100V
- $I_D$  100A
- $R_{DS(ON)}$  ( at  $V_{GS}=10V$ )  $< 8.0m\Omega$
- 100% EAS Tested
- 100%  $\nabla V_{DS}$  Tested

## General Description

- Trench Power MOSFET technology
- Excellent package for heat dissipation
- High density cell design for low  $R_{DS(ON)}$
- Moisture Sensitivity Level 1
- Epoxy Meets UL 94 V-0 Flammability Rating
- Halogen Free

## Applications

- Power switching application
- Uninterruptible power supply
- DC-DC convertor
- Motor drivers



## ABSOLUTE MAXIMUM RATINGS ( $T_J=25^\circ\text{C}$ unless otherwise noted)

| Parameter                                                          | Symbol          | Value     | Unit               |
|--------------------------------------------------------------------|-----------------|-----------|--------------------|
| Drain-Source Voltage                                               | $V_{DS}$        | 100       | V                  |
| Gate-Source Voltage                                                | $V_{GS}$        | $\pm 20$  | V                  |
| Continuous Drain Current ( $T_c=25^\circ\text{C}$ ) <sup>(1)</sup> | $I_D$           | 100       | A                  |
| Continuous Drain Current ( $T_c=100^\circ\text{C}$ )               | $I_D$           | 75        | A                  |
| Pulsed Drain Current <sup>(1)</sup>                                | $I_{DM}$        | 400       | A                  |
| Drain Power Dissipation                                            | $P_D$           | 180       | W                  |
| Single Pulsed Avalanche Energy <sup>(2)</sup>                      | $E_{AS}$        | 340       | mJ                 |
| Thermal Resistance from Junction to Ambient <sup>(3)</sup>         | $R_{\theta JA}$ | 43        | $^\circ\text{C/W}$ |
| Thermal Resistance from Junction to Case                           | $R_{\theta JC}$ | 1.0       | $^\circ\text{C/W}$ |
| Junction Temperature                                               | $T_J$           | -55~ +150 | $^\circ\text{C}$   |
| Storage Temperature                                                | $T_{STG}$       | -55~ +150 | $^\circ\text{C}$   |

### Notes:

- 1) Repetitive Rating: pulse width limited by maximum junction temperature
- 2) EAS condition :  $T_J=25^\circ\text{C}$ ,  $V_{DD}=50V$ ,  $V_G=10V$ ,  $L=1.0mH$ ,  $R_g=25\Omega$ ,  $I_{AS}=44.7A$
- 3) The value of  $R_{\theta JA}$  Mounted on FR4 Board (25.4mm\*25.4mm\*t1.6mm) With 2oz Copper  $T_A=25^\circ\text{C}$


**MOSFET ELECTRICAL CHARACTERISTICS(T<sub>J</sub>=25°C unless otherwise noted)**

| Parameter                          | Symbol               | Test Condition                                                                         | Min | Type | Max  | Unit |
|------------------------------------|----------------------|----------------------------------------------------------------------------------------|-----|------|------|------|
| Static Characteristics             |                      |                                                                                        |     |      |      |      |
| Drain-source breakdown voltage     | V <sub>(BR)DSS</sub> | V <sub>GS</sub> = 0V, I <sub>D</sub> =250μA                                            | 100 | -    | -    | V    |
| Zero gate voltage drain current    | I <sub>DSS</sub>     | V <sub>DS</sub> =100V, V <sub>GS</sub> = 0V                                            | -   | -    | 1    | μA   |
| Gate-body leakage current          | I <sub>GSS</sub>     | V <sub>GS</sub> =± 20V, V <sub>DS</sub> = 0V                                           | -   | -    | ±100 | nA   |
| Gate threshold voltage             | V <sub>GS(th)</sub>  | V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =250μA                               | 2.0 | 3.0  | 4.0  | V    |
| Drain-source on-resistance         | R <sub>DS(on)</sub>  | V <sub>GS</sub> =10V, I <sub>D</sub> =20A                                              | -   | 6.0  | 8.0  | mΩ   |
| Forward transconductance           | R <sub>g</sub>       | V <sub>GS</sub> = 0V, V <sub>DS</sub> = 0V, f=1.0MHz                                   | -   | 2.0  | -    | Ω    |
| Dynamic characteristics            |                      |                                                                                        |     |      |      |      |
| Input Capacitance                  | C <sub>iss</sub>     | V <sub>DS</sub> =50V, V <sub>GS</sub> =0V, f=1MHz                                      | -   | 4628 | -    | pF   |
| Output Capacitance                 | C <sub>oss</sub>     |                                                                                        | -   | 1624 | -    |      |
| Reverse Transfer Capacitance       | C <sub>rss</sub>     |                                                                                        | -   | 19   | -    |      |
| Switching characteristics          |                      |                                                                                        |     |      |      |      |
| Turn-on delay time                 | t <sub>d(on)</sub>   | V <sub>DD</sub> =50V, I <sub>D</sub> =20A, R <sub>G</sub> =3Ω,<br>V <sub>GS</sub> =10V | -   | 12   | -    | nS   |
| Turn-on rise time                  | t <sub>r</sub>       |                                                                                        | -   | 26   | -    |      |
| Turn-off delay time                | t <sub>d(off)</sub>  |                                                                                        | -   | 38   | -    |      |
| Turn-off fall time                 | t <sub>f</sub>       |                                                                                        | -   | 31   | -    |      |
| Total Gate Charge                  | Q <sub>g</sub>       | V <sub>DS</sub> =50V, I <sub>D</sub> =20A,<br>V <sub>GS</sub> =10V                     | -   | 61   | -    | nC   |
| Gate-Source Charge                 | Q <sub>gs</sub>      |                                                                                        | -   | 19.5 | -    |      |
| Gate-Drain Charge                  | Q <sub>gd</sub>      |                                                                                        | -   | 8.7  | -    |      |
| Source-Drain Diode characteristics |                      |                                                                                        |     |      |      |      |
| Diode Forward voltage              | V <sub>SD</sub>      | T <sub>J</sub> =25℃, V <sub>GS</sub> =0V, I <sub>S</sub> =20A                          | -   | 0.8  | 1.2  | V    |
| Diode Forward current              | I <sub>S</sub>       | T <sub>C</sub> =25℃                                                                    | -   | -    | 100  | A    |
| Body Diode Reverse Recovery Time   | trr                  | T <sub>J</sub> =25℃, I <sub>F</sub> =20A, di/dt=100A/us                                | -   | 77   | -    | nS   |
| Body Diode Reverse Recovery Charge | Qrr                  |                                                                                        | -   | 189  | -    | nC   |


**Ordering Information**

| Order number       | Package  | Marking     | Operation Temperature Range | MSL Grade | Ship, Quantity | Green |
|--------------------|----------|-------------|-----------------------------|-----------|----------------|-------|
| PSMN8R5-100PSQ-JSM | TO-220-3 | N8R5-100PSQ | -55 to 150°C                | 1         | T&R, 800       | RoHS  |


■ RATING AND CHARACTERISTIC CURVES




Peak Diode Recovery  $dv/dt$  Test Circuit




Peak Diode Recovery  $dv/dt$  Waveforms




Switching Test Circuit




Switching Waveforms




Gate Charge Test Circuit



Gate Charge Waveform



Unclamped Inductive Switching Test Circuit



Unclamped Inductive Switching Waveforms

## Typical Characteristics




Figure 1: Output Characteristics




Figure 2: Transfer Characteristics




Figure 3: On-Resistance vs. Gate-Source Voltage




Figure 4: On-Resistance vs. Drain Current




Figure 5: On-Resistance vs. Junction Temperature




Figure 6: Source-Drain Diode Forward Voltage

## Typical Characteristics




Figure 7: Gate Threshold Variation vs. Junction Temperature




Figure 8: Gate Charge Characteristics




Figure 9: Capacitance Characteristics




Figure 10: Power Derating




Figure 11: Current Derating




Figure 12: Safe Operating Area

## Typical Characteristics





Figure 13: Normalized Maximum Transient Thermal Impedance

Package Information

TO-220-3



Unit: mm

| Symbol | Size       |       | Symbol | Size  |       | Symbol | Size |      | Symbol | Size |      |
|--------|------------|-------|--------|-------|-------|--------|------|------|--------|------|------|
|        | Min        | Max   |        | Min   | Max   |        | Min  | Max  |        | Min  | Max  |
| W      | 9.66       | 10.28 | W5     | 9.80  | 10.20 | L4**   | 6.20 | 6.60 | T3     | 0.45 | 0.60 |
| W1     | 2.54 (TYP) |       | L      | 9.00  | 9.40  | L5     | 2.79 | 3.30 | G(Φ)   | 3.50 | 3.70 |
| W2     | 0.70       | 0.95  | L1     | 6.40  | 6.80  | T      | 4.30 | 4.70 |        |      |      |
| W3     | 1.17       | 1.37  | L2     | 2.70  | 2.90  | T1     | 1.15 | 1.40 |        |      |      |
| W4*    | 1.32       | 1.72  | L3     | 12.70 | 14.27 | T2     | 2.20 | 2.60 |        |      |      |

## Revision History

| Rev. | Change          | Date      |
|------|-----------------|-----------|
| V1.0 | Initial version | 9/17/2020 |
|      |                 |           |

## Important Notice

JSMSEMI Semiconductor (JSMSEMI) PRODUCTS ARE NEITHER DESIGNED NOR INTENDED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS UNLESS THE SPECIFIC JSMSEMI PRODUCTS ARE SPECIFICALLY DESIGNATED BY JSMSEMI FOR SUCH USE. BUYERS ACKNOWLEDGE AND AGREE THAT ANY SUCH USE OF JSMSEMI PRODUCTS WHICH JSMSEMI HAS NOT DESIGNATED FOR USE IN MILITARY AND/OR AEROSPACE, AUTOMOTIVE OR MEDICAL DEVICES OR SYSTEMS IS SOLELY AT THE BUYER' S RISK.

JSMSEMI assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using JSMSEMI products.

Resale of JSMSEMI products or services with statements diferent from or beyond the parameters stated by JSMSEMI for that product or service voids all express and any implied warranties for the associated JSMSEMI product or s ervice. JSMSEMI is not responsible or liable for any such statements.

JSMSEMI All Rights Reserved. Information and data in this document are owned by JSMSEMI wholly and may not be edited, reproduced, or redistributed in any way without the express written consent from JSMSEMI.

Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the JSMSEMI product that you intend to use.

For additional information please contact Kevin@jsmsemi.com or visit www.jsmsemi.com