


CUSTOMER :

CUSTOMER P/N:

DIAGRAM OF DIMENSIONS




Unit: mm

ϕ D	6.3
L	5.3 ± 0.2
A	6.6
B	6.6
C	7.2
W	0.5 ~ 0.8
P	2.0 ± 0.2

Items	Performance				
Category Temperature Range	-55℃ ~ +105℃				
Capacitance Tolerance	-20 % ~ +20 %				(120 Hz, 20℃)
Surge Voltage	18.4 VDC				
Leakage Current	I ≤ 16 μA				After 2 minutes
Tan δ	≤ 0.22				(120 Hz, 20℃)
Impedance	< 0.85 Ω				(100kHz, 20℃)
Ripple Current (rms)	170 mA				(100kHz, 105℃)
Low Temperature Characteristics(120 Hz)	Z(-25℃)/Z(+20℃)		2		
	Z(-55℃)/Z(+20℃)		5		
Ripple Current & Frequency Multipliers	Frequency (Hz)	50, 60	120	1k	10k up
	Multiplier	0.64	0.80	0.93	1.00
Life Test: Endurance: After 2000 Hrs at 105℃ Shelf Life Test: After 1000 Hrs at 105℃	Capacitance Change		Within ±25 % of initial value		
	Tan δ		Less than 200% of specified value		
	Leakage Current		Within specified value		
Standards	JIS C 5101-1, -18				
Remarks	RoHS Compliance & Halogen-free				

Marking: Each capacitor shall be marked with the following information.



2 A → January , 2012

Month of manufacture
The last digit of A. D.

Month	1	2	3	4	5	6
Code	A	B	C	D	E	F
Month	7	8	9	10	11	12
Code	G	H	I	J	K	L

Marking color: Black

* Please refer to " Precautions and Guidelines for Aluminum Electrolytic Capacitors " of Lelon's catalog.

Publish Date	February 8, 2014	Approval Signatures:	Approved	Checked	Designed
Revise Date			研發部 FEB 08 2014 蕭正浩	研發部 FEB 08 2014 陳 筱	研發部 FEB 08 2014 朱玉芳
Edition No.	1				

Please return one copy with your approval