





ROHS



MOUNTING PANEL CUTOUT(INTERNAL SIDE)



Pin No.	Signal Name
1	VBUS
2	D-
3	D+
4	GND
5	StdB_SSTX-
6	StdB_SSTX+
7	GND_DRAIN
8	StdB_SSRX-
9	StdB_SSRX+
SHELL	Shield

NOTE:

A. MATERIAL:



1. HOUSING: PA9T HF UL94V-0 COLOR:BLUE/BLACK
2. COVER: PA9T HF UL94V-0 COLOR:BLUE/BLACK
3. CONTACT: COPPER ALLOY
5. SHELL: S60C

B. PLATING:



1. CONTACT: CONTACT AREA GOLD PLATED
SOLDER AREA TIN PLATED
UNDER PLATED NICKEL
2. SHELL: NICKEL PLATED

C. SPECIFICATIONS:

1. CONTACT CURRENT RATING:
1.8A FOR PIN1&PIN4; 0.25A FOR OTHER PIN.
2. DIELECTRIC WITHSTANDING VOLTAGE: AC 100V(RMS)
3. INSULATION RESISTANCE: 100 MΩ MIN.
4. CONTACT RESISTANCE: 30 mΩ MAX. (PIN1,PIN4)
50 mΩ MAX. OTHER PIN
5. MATING AND UNMATING FORCE:
5.1 MATING FORCE: 35N MAX.
5.2 UNMATING FORCE: 10N MIN. INITIAL
8N MIN. AFTER DURABILITY
6. DURABILITY: 1500 CYCLES
7. SALT SPRAY: 24H
8. OPERATING TEMPERATURE: -20°C~+85°C



PCB LAYOUT(T=1.20)



RECESSED MOUNTING CONFIGURATION

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司		
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD		
CHECK					
APPROVAL					
TOLERANCES ARE			TITLE	TYPE-B连接器9PIN弯插L18.4（平口）	REV. A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-TYPE-B-9P-01-WC	UNITS mm
10-30	±0.2		DWG.NO.		
5-10	±0.15				
0-5	±0.1				
			Projection 		