


Transient Voltage Suppressors for ESD Protection

SE36D3S01GY

Features

- ◆ Protects one bi-directional I/O line
- ◆ Working voltage: 36V
- ◆ Low leakage current: 0.2 μ A @ V_{RWM}
- ◆ Low clamping voltage
- ◆ Response Time is < 1 ns


SOD-323



Applications

- ◆ Cell phone handsets and accessories
- ◆ Microprocessor based equipment
- ◆ Personal digital assistants (PDA's)
- ◆ Notebooks, desktops, and servers
- ◆ Portable instrumentation

Pin Configuration



Protection Solution to Meet

- ◆ IEC61000-4-2 (ESD) ± 30 kV (air), ± 30 kV (contact)
- ◆ IEC61000-4-4 (EFT) 40A (5/50ns)
- ◆ IEC61000-4-5 (Lightning) 4A (8/20 μ s)

Mechanical Characteristics

- ◆ SOD-323 package
- ◆ Molding compound flammability rating: UL 94V-0
- ◆ Weight 5 milligrams (approximate)
- ◆ Quantity per reel: 3,000pcs
- ◆ Lead finish: lead free

Absolute Maximum Ratings ($T_A=25^{\circ}\text{C}$, RH=45%-75%, unless otherwise noted)

Symbol	Parameter	Value	Units
T_{LST}	Lead Soldering Temperature	260 (10sec)	$^{\circ}\text{C}$
T_{STG}	Storage Temperature Range	-55 to +150	$^{\circ}\text{C}$
T_{OPT}	Operating Temperature Range	-55 to +150	$^{\circ}\text{C}$
V_{ESD}	ESD per IEC 61000-4-2(Air)	± 30	KV
	ESD per IEC 61000-4-2 (Contact)	± 30	

Transient Voltage Suppressors for ESD Protection

SE36D3S01GY

Electrical Characteristics (@T_A=25°C Unless Otherwise Specified)

Symbol	Test Condition	Minimum	Typical	Maximum	Units
V _{RWM}	--	--	--	36	V
I _R	V _{RWM} =36V, T=25°C	--	--	0.2	μA
V _{BR}	I _T = 1mA	40	--	47.5	V
V _C	I _{PP} =1A, t _p =8/20μs	--	50	--	V
V _C	I _{PP} =4A, t _p =8/20μs	--	64	--	V
C _J	V _R =0V, f=1MHz	--	13	--	pF

Ratings and V-I Characteristics Curves (T_A=25°C, unless otherwise noted)

Fig1. V-I Curve Characteristics (Bi-directional)




Fig2. Pulse Waveform (8/20μs)




Fig3. Pulse Derating Curve






Fig4. ESD Clamping (30kV Contact)



Transient Voltage Suppressors for ESD Protection

SE36D3S01GY

SOD-323 Package Outline Dimensions



Symbol	Millimeters		Inches	
	Min.	Max.	Min.	Max.
A	--	1.00	--	0.039
A1	0.00	0.10	0.000	0.004
A2	0.80	0.90	0.031	0.035
b	0.25	0.35	0.010	0.014
c	0.08	0.15	0.003	0.006
D	1.20	1.40	0.047	0.056
E	1.60	1.80	0.063	0.071
E1	2.55	2.75	0.100	0.108
L	0.475 REF.		0.019 REF.	
L1	0.25	0.40	0.010	0.016
θ	0°	8°	0°	8°

Warning



- ◆ SOCAY owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property.
- ◆ SOCAY reserves the right to make changes without further notice to any products herein.
- ◆ SOCAY makes no warranties, representations or warranties as to the fitness of its products for any particular purpose, and disclaims any liability.
- ◆ The parameters provided in the SOCAY datasheet specification may vary from application to application, and the actual performance may vary over time. All operating parameters must be verified by the customer's technical expert before application.
- ◆ Any and all responsibilities and liabilities are disclaimed if any item under this notice of warning is not complied with.