


Transient Voltage Suppressors for ESD Protection

SE08D3D01GN

Features

- ◆ IEC 61000-4-2 (ESD) $\pm 30\text{kV}$ (air), $\pm 30\text{kV}$ (contact)
- ◆ IEC 61000-4-4 (EFT) 40A (5/50ns)
- ◆ Response Time is $< 1\text{ns}$
- ◆ Protect one I/O line (bidirectional)
- ◆ Low clamping voltage
- ◆ Working voltage: 8V
- ◆ Low leakage current

SOD-323




Applications

- ◆ Cell Phone Handsets and Accessories
- ◆ Microprocessor based Equipment
- ◆ Personal Digital Assistants (PDA's)
- ◆ Notebooks, Desktops, and Servers
- ◆ Portable Instrumentation
- ◆ Peripherals
- ◆ USB Interface

Mechanical Characteristics

- ◆ SOD-323 Package
- ◆ Flammability Rating: UL 94V-0
- ◆ Packaging: 3000 PCS / Tape & Reel
- ◆ High Temperature Soldering Guaranteed: $260^{\circ}\text{C}/10\text{s}$
- ◆ Reel Size: 7 inch

Pin Configuration



Absolute Maximum Ratings (TA=25°C unless otherwise specified)

Parameter	Symbol	Value	Units
ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	V_{ESD}	± 30 ± 30	KV
Operating Temperature Range	T_{OPT}	$-55 \sim +125$	$^{\circ}\text{C}$
Storage Temperature Range	T_{STG}	$-55 \sim +150$	$^{\circ}\text{C}$
Lead Solering Temperature	T_{L}	260 (10 sec.)	$^{\circ}\text{C}$

Transient Voltage Suppressors for ESD Protection

SE08D3D01GN

Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise specified)

Part Number	V_{RWM} (V) (Max)	V_B (V) (Min)	I_T (mA)	$V_C @ 1A$ (V) (Typ)	V_C (V)		I_R (μA) (Max)	C_T (pF) (Typ)
					(Typ)	(@A)		
SE08D3D01GN	8.0	8.5	1	11	17	18	1	0.7

Electrical Characteristics Curves

Fig. 1. Pulse Waveform




Fig. 2. Non-Repetitive Peak Pulse Power vs. Pulse Time






Fig. 3. Power Derating Curve



Transient Voltage Suppressors for ESD Protection

SE08D3D01GN

SOD-323 Package Outline & Dimensions



Symbol	Millimeters			Inches		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	1.60	1.70	1.80	0.063	0.067	0.071
B	0.25	0.32	0.40	0.010	0.013	0.016
C	2.30	2.60	2.80	0.091	0.102	0.110
D	0.80	0.95	1.10	0.031	0.037	0.043
E	1.20	1.30	1.40	0.047	0.051	0.055
F	0.08	0.13	0.18	0.003	0.005	0.007
L	0.475REF			0.019REF		
L1	0.25	0.33	0.40	0.010	0.013	0.016
H	0.00	0.06	0.14	0.000	0.002	0.006

Warning



- ◆ SOCAY owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property.
- ◆ SOCAY reserves the right to make changes without further notice to any products herein.
- ◆ SOCAY makes no warranties, representations or warranties as to the fitness of its products for any particular purpose, and disclaims any liability.
- ◆ The parameters provided in the SOCAY datasheet specification may vary from application to application, and the actual performance may vary over time. All operating parameters must be verified by the customer's technical expert before application.
- ◆ Any and all responsibilities and liabilities are disclaimed if any item under this notice of warning is not complied with.