

A

B

C

D

E

F

技术要求/ Technical Requirement:

1.额定工作电压、电流/ Rating: 250V 15A.

2.插拔力/ Insertion force & Pull out force: 0.2~3N.

3.接触电阻/ Contact resistance $\leq 0.05 \Omega$.

4.适合保险丝管尺寸/ Applicable fuse size: $\phi 5.2^{+0.1}_{-0.2} \times 20 \pm 0.5 \text{mm}$.

5.机械寿命/ Mechanical life

用 $\phi 5$ 保险丝管连续插拔30次后, 插拔力和接触电阻仍符合要求。

It Satisfied to item 2 and 3 when instert and pull out the fuse from fuse clips, which were soldered to PC board, repeatedly 30 times.

6.可焊性/ Solderability

Sn99.3Cu0.7的锡炉在 $255^\circ\text{C} \pm 5^\circ\text{C}$ 情况下, 产品浸入 3 ± 0.5 秒, 表面75%能沾上锡。

Dip the terminals of the clip into solder (Sn99.3Cu0.7) bath at $255^\circ\text{C} \pm 5^\circ\text{C}$ for 3 ± 0.5 seconds. The dipped surfaces shall be covered with solder more than 75%.

7.不使用1级环境管理物质。

Not using substances banned in 1st grade of management regulations for environment-related substances.



8.材料 Material

镀锡黄铜 Tin plated brass

9.警告和注意/Warning and Caution

不要在含氨、强酸、强碱环境下使用, 以免发生材料腐蚀、断裂等不良现象。

Do not use the holder in ammonia, strong acid or strong alkali environment, it will cause the material corrosion or fracture.



2		
1	2016.10.12	增加警告与注意
NO.	REVISED DATE	REVISED DETAILS

		HOLLYLAND(CHINA)ELECTRONICS TECHNOLOGY CORPORATION LTD.	
		TITLE 保险丝管管夹 FUSE CLIP HF004/N	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MM		DRAWN BY	郑善烟 2016.10.12
DWG NO.	HLCP-H5-17A0	CHECKED BY	2016.10.12
MATERIAL		APPROVED BY	2016.10.12
TREATMENT			
QUANTITY			