


NO.	ECN NO.	DESCRIPTION	DATE
1			



Note:

- Material(材料):
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
- Plating(电镀):
Barrel: 50~100u' Ni(针管: 镀镍50~100u'。)
Plunger: 50~100'u Ni(针头: 镀镍50~100u'。)
Spring: No plated (弹簧: 不电镀)
- Electrical(电气特性):
Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧(在工作高度状态下)
- Mechanical(机械性能):
Force: 300g $\pm$ 20% at working height. (300g $\pm$ 20% 在工作行程时)。
Durability: 10.000 cycles(min) (寿命: 10000次)
- WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: - 40℃~ + 85℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZ92450330P-02
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:		TITLE:	Pogo pin
DATE:	2024.8.5	VER.	D.0	X.XX	$\pm 0.05\text{mm}$	X.XX	$\pm 0.50^\circ$	APPROVED BY:			
				X.X	$\pm 0.10\text{mm}$	X.X	$\pm 1.00^\circ$				
				X.	$\pm 0.20\text{mm}$	X.	$\pm 2.00^\circ$				