







ROHS



SPECIFICATION:

1. Material:

HOUSING&MOLDING:LCP,UL94 V-0

CONTACTS:C5191R-H/C2680-EH

PLANTING: Au G/F, Ni 40u", Sn 40u";

SHELL:SUS,T=0.30

PLANTING:Ni 40u";

2. Mechanical:

2.1.Mating force:5~20Nf Max.;

2.2.Unmating force:6~20Nf Min.;

2.3.Durability:3000 Cycles;

3.Electrical:

3.1.Current Rating:3A Max.;

3.2.Voltage Rating:20V Max.;

3.3.Dielectric Withstanding voltage:100VAc;


3.4.Contact resistance:40m Ohms Max.;

3.5.Insulation Resistance:100M Ohms Min.;

4.Environmental:

4.1.Operating temperature:-40°C~+85°C;

4.2.Wetting Temperature:265±5°C,5±0.5s





COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	TYPE-C连接器6PIN立贴H6.8	REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-TYPE-C-6PIN-01Y-LT	UNITS	mm
10-30	±0.2		DWG.NO.		Projection	
5-10	±0.15					
0-5	±0.1					

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- 说明:
- 1.每卷前后各空15PCS,尾部用美纹胶纸封住;
 - 2.将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
 - 3.每10卷盘一叠共12000Pcs装入1个外箱内;
 - 4.在搬运过程中要轻拿轻放;
 - 5.在运输中不可堆放过多(1.8M最高),不可重压;
 - 6.跌落测试条件:
成品箱从1.2米高度自由落体(一角三棱六面):
a.产品不可跑出下带凹槽;
b.产品不可有摔伤,变形;
c.内包装材料不可严重破损.



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司				
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECK						
APPROVAL						
TOLERANCES ARE		TITLE	TYPE-C连接器6PIN立贴H6.8	REV.	A	
30-150	±0.35	PART NO.	LAIL-TYPE-C-6PIN-01Y-LT	UNITS	mm	
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
ANGLE		DWG.NO.		Projection		
±3°						