


NO.	ECN NO.	DESCRIPTION	DATE
		首次发行	2014.10.22

客户图



- Note:
- 1: Material(材料) :
Housing&Cap: PA46+30%GF (胶芯&胶盖: PA46)
Barrel: Brass C3604 (针管: 黄铜 C3604)
Plunger: Brass C3604 (针头: 黄铜 C3604)
Spring: SUS304 (弹簧: SUS304)
 - 2: Plating(电镀) :
Barrel: 3u' Au over 50~80u' Ni(针管: 镀金3u', 镍底50~80u'.)
Plunger: 3u' Au over 50~80u' Ni (针头: 镀金3u', 镍底50~80u'.)
Spring: No plated (弹簧: 不电镀)
 - 3: Electrical(电气特性) :
Rated Current & Voltage: DC 12V;1A (额定电压&电流: 直流12V,1A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
Insulation Resistance: 1,000MΩ minimum. (绝缘电阻: 1,000MΩ以上)
Dielectric Withstand Voltage: 500VAC/minute. (抗击电压: 500VAC/minute)
 - 4: Mechanical(机械性能) :
Force: 130g±20% at working height. (130g±20% 在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
 - 5: WorkTemperture(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: -20℃~ +70℃

RECOMMENDED PCB LAYOUT

深圳市鑫扬泽电子有限公司

HTTP://WWW.XYZPOGOPIN.COM

TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:		DWG. NO.	YZ78515030R-03025-01
SHEET:	1 of 1	PROJECTION						CHECKED BY:		TITLE:	Pogo pin 连接器
DATE:	2014.10.22	VER.	A.0	LENGTH				APPROVED BY:			
				ANGLE							
				X.XX	±0.05mm	X.XX	±0.50°				
				X.X	±0.10mm	X.X	±1.00°				
				X.	±0.20mm	X.	±2.00°				