





TABLE:

| NO. | PART NO.           | DESCRIPTION                                          | DURABILITY |
|-----|--------------------|------------------------------------------------------|------------|
| 1   | 26004-S20674BGF14R | GOLD G/F ON CONTACT AREA<br>GOLD G/F ON SOLDER AREA  | 25 CYCLES  |
| 2   | 26004-S20674BG614R | GOLD 10u" ON CONTACT AREA<br>GOLD G/F ON SOLDER AREA | 25 CYCLES  |
| 3   | 26004-S20674BG714R | GOLD 15u" ON CONTACT AREA<br>GOLD G/F ON SOLDER AREA | 25 CYCLES  |
| 4   | 26004-S20674BG814R | GOLD 30u" ON CONTACT AREA<br>GOLD G/F ON SOLDER AREA | 60 CYCLES  |

3D VIEW

## Notes:

- MATERIAL SPECIFICATION:
  - HOUSING:LCP+40%GF,UL94V-0,COLOR:BLACK.
  - CONTACT:COPPER ALLOY.
  - PEG:STEEL.
- PLATING SPECIFICATION:
  - CONTACT:50u" MIN.NICKEL UNDER PLATING  
OVER ALL.PLATING ON SOLDER AREA:SEE TABLE  
GOLD PLATING ON CONTACT AREA:SEE TABLE
  - PEG:50u" MIN. NICKEL UNDER PLATING OVER ALL.  
80u" MIN. MATTE TIN PLATING ON SOLDER AREA.
- HF COMPLIANT, RoHS COMPLIANT.
- DATE CODE: XX XX XX  
DAY  
WEEK  
YEAR
- MECHANICAL PERFORMANCE:
  - DURABILITY: SEE TABLE
- ELECTRICAL PERFORMANCE:
  - CURRENT: 0.5A PER PIN.
  - LLCR: INITIAL 55mΩ MAX.;FINAL ΔLLCR=20mΩ MAX.
- IR REFLOW:  
THE TEMPERATURE SHALL BE 260±5°C MAINTAINING 10±1 SECONDS.

RoHS  
Compliant  
2013/95/EC



|                                                                         |                                                                                       |                                                                                                                                                             |                                          |             |           |                 |
|-------------------------------------------------------------------------|---------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------|-------------|-----------|-----------------|
| CUSTOMER<br>DRAWING                                                     |                                                                                       |  连兴旺电子(深圳)有限公司<br>connectivity LXWCONN ELECTRONICS (SHENZHEN) CO., LTD |                                          |             |           |                 |
| GENERAL<br>TOLERANCE<br>.X ±0.35<br>.XX ±0.25<br>.XXX ±0.15<br>ANGLE±3° |                                                                                       | DESIGN Tan<br>2026.05.12                                                                                                                                    | TITLE<br>0.5Pitch 67pin M.2 H6.7 (KEY B) |             |           |                 |
| CHECKED Tan<br>2026.05.12                                               |                                                                                       | PART NO.<br>26004-S20674BXX14R                                                                                                                              |                                          |             |           |                 |
| SIZE<br>A4                                                              |  | APPROVAL Tan<br>2026.05.12                                                                                                                                  | SCALE<br>1:1                             | UNITS<br>MM | REV.<br>A | SHEET<br>2 OF 5 |

