





REV.	DESCRIPTION	ECN NO.	NAME	DATE

序号	品名	材质
1	2.0A型双排立式WTB胶芯	PA46 UL94V-0 白色
2	2.0F型卧式2代WTB端子	铜合金/表面镀锡

Part No	Pin	A	B	C
WF-1A200H4P	2*2	2.0	6.0	3.2
WF-1A200H6P	2*3	4.0	8.0	3.2
WF-1A200H8P	2*4	6.0	10.0	3.0
WF-1A200H10P	2*5	8.0	12.0	5.0
WF-1A200H12P	2*6	10.0	14.0	7.0
WF-1A200H14P	2*7	12.0	16.0	9.0
WF-1A200H16P	2*8	14.0	18.0	11.0
WF-1A200H18P	2*9	16.0	20.0	13.0
WF-1A200H20P	2*10	18.0	22.0	15.0
WF-1A200H22P	2*11	20.0	24.0	17.0
WF-1A200H24P	2*12	22.0	26.0	19.0
WF-1A200H26P	2*13	24.0	28.0	21.0
WF-1A200H28P	2*14	26.0	30.0	23.0
WF-1A200H30P	2*15	28.0	32.0	25.0
WF-1A200H32P	2*16	30.0	34.0	27.0
WF-1A200H34P	2*17	32.0	36.0	29.0
WF-1A200H36P	2*18	34.0	38.0	31.0
WF-1A200H38P	2*19	36.0	40.0	33.0
WF-1A200H40P	2*20	38.0	42.0	35.0
WF-1A200H42P	2*21	40.0	44.0	37.0
WF-1A200H44P	2*22	42.0	46.0	39.0

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 工作温度: $-40^{\circ}\text{C}\sim 105^{\circ}\text{C}$ 。
3. 额定电压: 250V DC/AC(rms)。
4. 额定电流: 3.0A AC,DC。
5. 接触电阻: $\leq 20\text{m}\Omega$ 。
6. 耐压值: 800V AC/minute。
7. 绝缘电阻: $\geq 1000\text{M}\Omega$ 。

GENERAL TOLERANCE		DONGGUAN BAOXUN PRECISION TECHNOLOGY CO., LTD					BXCONN®	
DIM. TOL. .X ±0.20 .XX ±0.10 .XXX ±0.05		TITLE: 2.00 Pitch A型双排直插						
GENERAL ANGLE: X° ±2° X.X°		DWG. NO.: WF-1A200HXP			CHECKED: MAX			
		PART NO.: WF-1A200HXP			DRAWN: ELLA			
		UNIT: mm			APPROVED: WILL			
		SCALE: none						
		SHEET: 1 of 1		DWG. SIZE: A4		LAYER: bxconn		