



深圳市佑驰电子有限公司

Specification for Approval

产品名称: 合金磁胶电感

规格型号: HNRS252012Z Series

产品编号: _____

日期: 2026/4/3

- 1、本承诺书的内容更改需经过双方确认，任一方单独的修改均视为无效。
- 2、本承诺书在送达客户后，请给予承认并即签回，如无签回下订单的，我司有权以此承认书标准生产，并表示购买方默认许可。


核准	审核	制作
	Aaron	Ada

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 1/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

1.SHAPE & DIMENSION


UNIT: mm

SCHEMATICS



MARKING
COLOR

NA



A	B	C	D	E	P1	P2	P3
2.5	2	2.5	1.25	1.05	2.9	2.4	0.8
0.3/-0.1	0.3/-0.1	0.3/-0.1	MAX	±0.25	Ref.	Ref.	Ref.

PART NUMBERING SYSTEM

HNRS 252012 Z - 2R2 M C
1 2 3 4 5 6

1 PRODUCT CATEGORY (产品种类)

2 DIMENSIONS (尺寸规格)

NR-镍锌 NRS-合金

3 MAERTIAL TYPE (材料类型) A-四边 B-八边 Z-十二边

4 INDUCTANCE (电感量)

5 TOLERANCE (公差)

M:±20% N:±25% Y:±30%

6 PACKAGING (包装方式)

C - 编带盘装 B - 盒装

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 2/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

2.SERIES SPECIFICATION

◆ HNRS252012Z Series Specification:

Part Number	Inductance	Test Freq	DCR(mΩ)		Saturation Current (A)		Temp. Rise Current (A)	
	(μH)	(Hz)	Max	Typ	Max	Typ	Max	Typ
HNRS252012Z-R24YC	0.24	1MHz/1V	25	19	7.00	8.50	4.05	4.70
HNRS252012Z-R33YC	0.33		35	24	6.00	7.00	3.70	4.30
HNRS252012Z-R47YC	0.47		39	29	5.10	5.80	3.45	4.00
HNRS252012Z-R68YC	0.68		43	36	3.90	4.50	3.15	3.60
HNRS252012Z-1R0YC	1.00		80	60	3.10	4.00	2.30	2.50
HNRS252012Z-1R5YC	1.50		100	80	2.90	3.50	2.10	2.40
HNRS252012Z-2R2MC	2.20		120	100	2.40	3.00	1.90	2.15
HNRS252012Z-3R3MC	3.30		176	146	1.70	2.10	1.50	1.80
HNRS252012Z-4R7MC	4.70		260	225	1.60	1.90	1.25	1.45
HNRS252012Z-6R8MC	6.80		366	305	1.15	1.35	0.95	1.10
HNRS252012Z-100MC	10.0		550	450	1.10	1.35	0.85	1.00

◆ TEST CONDITION

ITEM	TEST CONDITION	TEST INSTRUMENTS
L	1MHz/1V	Microtest 6377
Isat		TH1773+Microtest 6377
Irms		
DCR	25±5℃	TH2512B

*The operating temperature is 25℃

*Isat: For Inductance drop 30% from its value without current

*Irms: The value of D.C current when the temperature rise is $\Delta T \leq 40^\circ\text{C}$. ($T_a = 25^\circ\text{C}$)

*For HNRS252012Z Series size inductors, absolute maximum voltage: DC 25 V.

※此物料仅用于消费电子领域, 若用于车载, 航天, 军事领域引起的一切品质和责任问题, 我司既不承担※

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 3/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

3.MATERIAL LIST & GENERAL SPECIFICATION

材料名称	型号及规格	制造商	环保要求	备注
ITEM	Materials	Manufacturer	EN.QU	Note
磁芯1 (Drum Core)	合金 (Alloy)	DJ	RoHS	Primary
铜线 (Wire)	Polyester Wire or equivalent	ELEKTRISOLA	RoHS	
胶水 (Glue)	Phenolic epoxy resin	DAJOO	RoHS	
锡 (Solder)	107H	QD	RoHS	Primary
锡 (Solder)	107H	TF	RoHS	Alternative

GENERAL SPECIFICATION	
Electrical specifications :	at 20~25°C
Operation Temperature :	-40~+125°C
Storage Temperature :	-40~+125°C

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 4/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3


4.PACKAGING(unit: mm)

1.包装类型


2.包装尺寸

13" 盘



7" 盘



	13" 盘	7" 盘
A	$\Phi 330 \pm 2.0$	$\Phi 178 \pm 2.0$
D	8.4	




Peel-off strength: 10~100gf.
Peel-off angle: 165°-180°
Peel-off speed: 300mm/min.



产品摆放方向顶视图


底视图



Item	W	B0	P	T	E	F	D0	P0	K0	
DIM(mm)	8.0±0.3	2.95±0.1	4.0±0.1	0.3±0.05	1.75±0.1	3.5±0.1	1.5±0.1	4.0±0.1	1.4±0.1	

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 5/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

5. CARTON



1.1 外箱: 40*40*17 cm 一纸托装一箱

1.2 内箱: CAG002(装7寸卷盘TRAY盘)

1.3 外箱材质: A三A

1.4 内箱材质: A=A

1.5 每10卷制品用一只静电袋包装

1.6 每一静电袋内放一只袋干燥剂

1.7 每一卷上面依标签样式的要求贴上标签明细

1.8 出货内外箱贴上该箱内实际内容明细

1.9 出货标签规格如下: 尺寸=长度:39mm 宽度:29mm

(如: 客户有特殊要求时, 则依客户要求实施.)

储存条件及期限:

温度: 20-25℃

湿度: ≤70%

时间: 六个月

卷轴包装数量

每卷	2000	PCS
----	-------------	-----

外箱包装数量

每箱	40	卷,共	80000	PCS
----	-----------	-----	--------------	-----

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 6/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

6. RELIABILITY TEST

Test Items	Test Conditions	Criteria
1 Low temperature storage	Placed at -40°C for 500 hours, then measured at room ambient temperature after placing 24hours	Inductance shall be within $\pm 10\%$ of the initial value.
2 High temperature storage	Placed at +125°C for 500 hours, then measured at room ambient temperature after placing 24 hours	Inductance shall be within $\pm 10\%$ of the initial value.
3 Thermal shock	Condition for 1 cycle: -40°C,30min.~+125°C,30min Number of cycles:5	Inductance shall be within $\pm 10\%$ of the initial value.
4 Humidity resistance	Placed at 90 to 95%RH,+50°C for 500 hours, then measured at room ambient temperature after placing 24 hours.	Inductance shall be within $\pm 10\%$ of the initial value. Insulation resistance > 100MΩ at DC
5 Drop	Drop specimen three times on concrete floor from a height of 1 meter which mounted on test board	Inductance shall be within $\pm 10\%$ of the initial value.
6 Vibration	Frequency::10~55~10Hz Amplitude:1.5mm or 10G Sweep time: 1 oct/min Test Directions: X,Y,Z Test Time: 2 hours each direction	Inductance shall be within $\pm 10\%$ of the initial value.
7 Terminal strength	Add static load 4.9N(500gf) to inductor through hole of test board for 10±2 sec.	No detachment of terminal pin and no breakage of wire
8 Soldering heat resistance	Dip Inductor's terminal in solder bath of following conditions: 1) 260±5°C, 10±1 sec, 2) 350±10°C, 3.5±0.5 sec	Inductance shall be within $\pm 10\%$ of the initial value. Apperance: No damage

CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 7/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

7. SOLDERING CONDITIONS


Applicable soldering process to the products is refl.

9.1 Soldering Materials

(1) Solder: Sn-3.0Ag-0.5Cu

(2) Flux: Use rosin-based flux, but not strongly acidic flux (with chlorine exceeding 0.2wt%). Do not use water-soluble flux.

9.2 Reflow Soldering Profile



9.3 Soldering Iron

Reworking with electric soldering iron must preheating at 150°C for 1 minute is required, and do not directly touch the core with the tip of the soldering iron. The reworking soldering conditions are as follows.

- ① Temperature of soldering iron tip: 350°C;
- ② Soldering iron power output: ≤30W;
- ③ Diameter of soldering iron end: ≤1.0mm;
- ④ Soldering time: <3 s




CUSTOMER	0	REVISION NO.	A
CUSTOMER'S P/N	0	PAGE	P 8/8
DESCRIPTION.	SMD POWER INDUCTOR	DRAWN NO.	0
PART NO.	HNRS252012Z Series	DATE	2026/4/3

8.Appearance of the standard

1.Void appearance tolerance limit

Size of voids occurring to coating resin is specified below.




①Width direction(dimension A): Acceptable when $A \leq C/2$

Nonconforming when $B \geq C/2$


②Length direction(dimension B):Dimension b is not specified

③When total area of voids (including one exposing coil) occurring to each sides is not greater than 50% of coating resin area,that is acceptable.

2.External appearance criterion for exposed wire



Exposed end of the winding wire at the secondary side should be 3.0mm and below.



①Acceptable when $A \leq 0.8\text{mm}$

②Nonconforming when $A > 0.8\text{mm}$