


SURFACE MOUNT ULTRAFAST RECOVERY RECTIFIER
Reverse Voltage - 50 to 1000 V
Forward Current - 1 A
FEATURES


- For surface mounted applications
- Low profile package
- Glass Passivated Chip Junction
- High efficiency
- Lead free in comply with EU RoHS 2011/65/EU directives

MECHANICAL DATA

- Case: SOD-123FL
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight: 15mg/0.00053oz

PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode


Maximum Ratings and Electrical characteristics

Ratings at 25 °C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derate by 20 %.

Parameter	Symbols	US1AW	US1BW	US1DW	US1GW	US1JW	US1KW	US1MW	Units
Maximum Repetitive Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current at T _c = 125 °C	I _{F(AV)}	1							A
Peak Forward Surge Current 8.3 ms Single Half Sine Wave Superimposed on Rated Load	I _{FSM}	30							A
Maximum Instantaneous Forward Voltage at 1 A	V _F	1.0			1.3	1.65			V
Maximum DC Reverse Current at Rated DC Blocking Voltage	I _R	5 100							μA
Maximum Reverse Recovery Time ⁽¹⁾	t _{rr}	50				75			ns
Typical Junction Capacitance ⁽²⁾	C _j	15							pF
Typical Thermal Resistance ⁽³⁾	R _{θJA}	85							°C/W
Operating and Storage Temperature Range	T _j , T _{stg}	-55 ~ +150							°C

(1) Measured with $I_F = 0.5\text{ A}$, $I_R = 1\text{ A}$, $I_{rr} = 0.25\text{ A}$.

(2) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(3) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.



Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristics




Fig.4 Maximum Non-Repetitive Peak Forward Surge Current




Fig.5- Typical Transient Thermal Impedance





Fig.6 Typical Junction Capacitance






PACKAGE OUTLINE


Plastic surface mounted package; 2 leads

SOD-123FL



UNIT		A	C	D	E	e	g	B	$\angle$
mm	max	1.15	0.20	2.8	2.0	1.2	0.9	3.8	5°
	min	0.95	0.12	2.5	1.7	0.9	0.7	3.5	
mil	max	45	7.9	110	78.7	47	35	150	
	min	37	4.7	98	67	35	28	138	

The recommended mounting pad size



Marking

Type number	Marking code
U1A	U1A
U1B	U1B
U1D	U1D
U1G	U1G
U1J	U1J
U1K	U1K
U1M	U1M