





- SPECIFICATION:
1. Material & Finish: See the list;
  2. Mechanical:
    - 2.1. Mating force: 5-20Nf;
    - 2.2. Unmating force: 6-20Nf;
    - 2.3. Durability: 3000 Cycles;
  3. Electrical:
    - 3.1. Current Rating: 3A Max.;
    - 3.2. Voltage Rating: 20V Max.;
    - 3.3. Dielectric Withstanding voltage: 100Vac;
    - 3.4. Contact resistance: 40m Ohms Max.;
    - 3.5. Insulation Resistance: 100M Ohms Min.;
  4. Environmental:
    - 4.1. Operating temperature: -40° C ~ +85° C;
    - 4.2. Salt Spray Test: 24H Min. (No oxidation or rust);
    - 4.3. Wetting Temperature: 265 ± 5° C, 5 ± 0.5s



|     |        |     |        |
|-----|--------|-----|--------|
| A5  | CC1    | B5  | CC2    |
| A9  | VBUS   | B9  | VBUS   |
| A12 | GND    | B12 | GND    |
| PIN | SIGNAL | PIN | SIGNAL |

| PN.                |           | DESCRIPTION                                       |                 |           |
|--------------------|-----------|---------------------------------------------------|-----------------|-----------|
| 11013-S10064BCG00R |           | 塑胶LCP黑色, 外壳SUS201脚长0.95, 端子C5191接触区镀金1u", 焊脚镀金G/F |                 |           |
| 11013-S10064BC300R |           | 塑胶LCP黑色, 外壳SUS201脚长0.95, 端子C5191接触区镀金3u", 焊脚镀金3u" |                 |           |
| 11013-S10064WC300R |           | 塑胶LCP白色, 外壳SUS201脚长0.95, 端子C5191接触区镀金3u", 焊脚镀金3u" |                 |           |
| NO.                | PART NAME | Q' TY                                             | MATERIAL        | FINISH    |
| 3                  | Shell     | 1                                                 | SUS201 T=0.30mm | Ni        |
| 2                  | Housing   | 1                                                 | LCP             | UL 94 V-0 |
| 1                  | Contact   | 1                                                 | C5191 T=0.20mm  | Au        |

CUSTOMER  
DRAWING

GENERAL  
TOLERANCE  
.X ±0.30  
.XX ±0.25  
.XXX ±0.10  
ANGLE ±0.5°

DESIGN ZHU  
2026.04.07

CHECKED

APPROVAL

SCALE  
1:1

UNITS  
MM

REV.  
A






SHEET  
1 OF 1

连兴旺电子(深圳)有限公司

LXWCONN ELECTRONICS(SHENZHEN)CO., LTD

TPC6P SMT 全包  
板上平贴L6.80 (不露铜) 成品

PART NO.  
11013-S10064XXX00R



说明:

- 每卷前后各空16PCS, 尾部用美纹胶纸封住;
- 将产品放满盘后, 再卷一圈保护带, 用美纹胶纸将其封住, 并贴上1Pcs物料标签;
- 每15卷盘一叠共15000Pcs装入1个外箱内;
- 在搬运过程中要轻拿轻放;
- 在运输中不可堆放过多(1.8M最高), 不可重压;
- 跌落测试条件:  
成品箱从1.2米高度自由落体(一角三棱六面):  
a. 产品不可跑出下带凹槽;  
b. 产品不可有摔伤, 变形;  
c. 内包装材料不可严重破损.

| NO. | NAME              | SPEC             | Q' TY           |
|-----|-------------------|------------------|-----------------|
| ①   | TYPE C RECEPTACLE |                  | 15000PCS/CARTON |
| ②   | CARRIER TAPE      | W=16mm, T=0.40mm | 1000PCS/PLATE   |
| ③   | COVER TAPE        | W=13.2mm         | 15PLATES/CARTON |
| ④   | REEL PLATE        | 330*100*16.4mm   | 15PCS/CARTON    |
| ⑤   | RoHS LABEL        |                  | 15PCS/CARTON    |
| ⑥   | PRODUCT LABER     |                  | 15PCS/CARTON    |
| ⑦   | CARTON            | 340*340*325mm    | 1PCS/PACKAGE    |

|                                                                           |                                                                                       |                                                                                                                                                            |                                             |             |                 |
|---------------------------------------------------------------------------|---------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------|-------------|-----------------|
| CUSTOMER<br>DRAWING                                                       |                                                                                       |  连兴旺电子(深圳)有限公司<br>connectivity LXWCONN ELECTRONICS(SHENZHEN) CO., LTD |                                             |             |                 |
| GENERAL<br>TOLERANCE<br>.X ±0.30<br>.XX ±0.25<br>.XXX ±0.10<br>ANGLE±0.5° |                                                                                       | DESIGN<br>ZHU<br>2026.04.07                                                                                                                                | TITLE<br>TPC6P SMT 全包<br>板上平贴L6.80 (不露铜) 成品 |             |                 |
| CHECKED                                                                   |                                                                                       | PART NO.<br>11013-S10064XXX00R                                                                                                                             |                                             |             |                 |
| SIZE<br>A4                                                                |  | APPROVAL                                                                                                                                                   | SCALE<br>1:1                                | UNITS<br>MM | REV.<br>A       |
|                                                                           |                                                                                       |                                                                                                                                                            |                                             |             | SHEET<br>1 OF 1 |