








ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

1. MATERIAL & FINISH:SEE THE LIST;
2. PLATING SPECIFICATION:
 - 2-1.CONTACTS:
Ni 50u" MIN. UNDER PLATED OVER ALL.
Au PLATED ON THE MATING AREA OF CONTACT.
Sn PLATED ON THE SOLDER AREA.
 - 2-2.SHELL:Ni 30u" MIN. UNDER PLATED OVER ALL.
 - 2-3.MID PLATE:CLEAR ONLY
3. MECHANICAL:
 - 3.1.MATING FORCE:0.5~2.0kgf;
 - 3.2.UNMATING FORCE:0.8~2.0kgf.
0.6~2.0kgf AFTER DURABILITY TEST;
 - 3.3.DURABILITY:10000 CYCLES;
- 4.ELECTRICAL:
 - 4.1.CURRENT RATING:3A/5A Max;
 - 4.2.VOLTAGE RATING:20V Max;
 - 4.3.DIELECTRIC WITHSTANDING VOLTAGE:100Vac;
 - 4.4.CONTACT RESISTANCE:40mΩ Ohms Max.;
 - 4.5.INSULATION RESISTANCE:100M Ohms Min.;
- 5.ENVIRONMENTAL:
 - 5.1.OPERATING TEMPERATURE:-40°C~+85°C;
 - 5.2.WETTING TEMPERATURE:265±5°C,5±0.5s
 - 5.3.Salt Spray Test:24H/48H Min



PIN DEFINE TABLE			
PIN	SIGNAL	PIN	SIGNAL
A12	GND	B1	GND
A11		B2	
A10		B3	
A9	VBUS	B4	VBUS
A8	SBU1	B5	CC2
A7	D-	B6	D+
A6	D+	B7	D-
A5	CC1	B8	SBU2
A4	VBUS	B9	VBUS
A3		B10	
A2		B11	
A1	GND	B12	GND



NO.	PART NAME	Q' TY	MATERIAL	FINISH												
4	Shell	1	Stainless Steel, T=0.30mm	30u"Ni Min.												
3	GroundBar	1	Stainless Steel, T=0.15mm	No Plating												
2	Contact	14	Copper Alloy, T=0.15mm	Au/Sn/Ni-Plated												
1	Housing	1	High temperature plastic	UL94 V=0, Black												
COSTOMER DRAWING		 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD														
DRAWING		<table><tr><td>TITLE</td><td>TYPE-C连接器16PIN直插H10.0</td><td>REV.</td><td>A</td></tr><tr><td>PART NO.</td><td>LAIL-TYPE-C-16PIN-02Y-ZC</td><td>UNITS</td><td>mm</td></tr><tr><td>DWG.NO.</td><td></td><td>Projection</td><td></td></tr></table>			TITLE	TYPE-C连接器16PIN直插H10.0	REV.	A	PART NO.	LAIL-TYPE-C-16PIN-02Y-ZC	UNITS	mm	DWG.NO.		Projection	
TITLE	TYPE-C连接器16PIN直插H10.0				REV.	A										
PART NO.	LAIL-TYPE-C-16PIN-02Y-ZC				UNITS	mm										
DWG.NO.					Projection											
CHECK																
APPROVAL																
TOLERANCES ARE																
30-150	±0.35	ANGLE	±3°													
10-30	±0.2															
5-10	±0.15															
0-5	±0.1															

SHENZHEN LAILIAN ELECTRONICS CO., LTD








REV.	ECN NO.	DESCRIPTION	DRAW	DATE

说明:

- 1.每卷前后各空16PCS,尾部用美纹胶纸封住;
- 2.将产品放满盘后,再卷一圈保护带,用美纹胶纸将其封住,并贴上1Pcs物料标签;
- 3.每10卷盘一叠共5000Pcs并装入1个外箱内;
- 4.在搬运过程中要轻拿轻放;
- 5.在运输中不可堆放过多(1.8M最高),不可重压;
- 6.跌落测试条件:

成品箱从1.2米高度自由落体(一角三棱六面):

- a.产品不可跑出下带凹槽;
- b.产品不可有摔伤,变形;
- c.内包装材料不可严重破损.



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	TYPE-C连接器16PIN直插H10.0	REV.	A		
30-150	±0.35	PART NO.	LAIL-TYPE-C-16PIN-02Y-ZC	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG.NO.		Projection			
±3°							