




ROHS



PCB LAYOUT

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATION:

Current Rating : 3AMP

Temperature Range : -40°Cto+105°C

Contact Resistance : 20mΩ Max

Insulation Resistance : 1000MΩ Min

Withstanding Voltage : AC 1000V


Material:

Insulator : Polyester (UL94V-0)

Standard: PA9T

Contact: Brass

Plating : Au over Ni



CUSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD			
DRAWING			TITLE筒牛 PIN距2.54 塑高8.9 双排6PIN 直插REV.A			
CHECKED						
APPROVED						
TOLERANCES ARE			PART NO.LAIL-SI-2.54-2X6P-ZCUNITSmm			
30-150	±0.35	ANGLE	DWG. NO.Projection 			
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					