


DO-27



Dimensions in inches and (millimeters)

FEATURES

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ For surface mounted applications
- ◆ Low reverse leakage
- ◆ Built-in strain relief, ideal for automated placement
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 250°C/10 seconds at terminals
- ◆ Glass passivated chip junction

MECHANICAL DATA

Case: JEDEC DO-27 molded plastic body over passivated chip

Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Mounting Position: Any

Weight: 0.82 grams

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

	SYMBOLS	MUR420	MUR440	MUR460	UNITS
Maximum repetitive peak reverse voltage	V _{RRM}	200	400	600	VOLTS
Maximum RMS voltage	V _{RMS}	140	280	420	VOLTS
Maximum DC blocking voltage	V _{DC}	200	400	600	VOLTS
Maximum average forward rectified current at T _L =55°C	I _(AV)	4.0			Amps
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	100.0			Amps
Maximum instantaneous forward voltage at 4.0A	V _F	0.90	1.30		Volts
Maximum DC reverse current T _A =25°C at rated DC blocking voltage T _A =100°C	I _R	5.0 150.0			μA
Maximum reverse recovery time (NOTE 1)	t _{rr}	35	50		ns
Typical junction capacitance (NOTE 2)	C _J	75	63		pF
Typical thermal resistance (NOTE 3)	R _{θJA}	47.0			°C/W
Operating junction and storage temperature range	T _J ,T _{STG}	-65 to +150			°C


Note: 1. Reverse recovery condition $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $t_{rr}=0.25\text{A}$

2. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

3. P.C.B. mounted with 0.2x0.2" (5.0x5.0mm) copper pad areas

AVERAGE FORWARD RECTIFIED CURRENT,
AMPERES

FIG. 1- FORWARD CURRENT DERATING CURVE



PEAK FORWARD SURGE CURRENT,
AMPERES

FIG. 2-MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT





FIG. 3-TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS



INSTANTANEOUS REVERSE CURRENT,
MICROAMPERES

FIG. 4-TYPICAL REVERSE CHARACTERISTICS






FIG. 5-TYPICAL JUNCTION CAPACITANCE



TRANSIENT THERMAL IMPEDANCE,
°C/W

FIG. 6-TYPICAL TRANSIENT THERMAL IMPEDANCE



请仔细阅读

感谢您使用或即将使用本公司的产品。建议您在使用前仔细阅读本资料。

- 本公司竭力为用户提供更优质的产品与服务。
- 江苏信达兴微电子有限公司会不定期的优化产品及相应规格书，也许无法及时通知到您，请定期下载最新的版本。
- 江苏信达兴微电子有限公司对任何将其产品用于特殊目的的行为不承担任何责任与风险。
- 江苏信达兴微电子有限公司对自身的产品拥有专利权。
- 任何半导体产品在特定条件下都有一定的失效或发生故障的可能。买方在使用江苏信达兴微电子有限公司产品进行系统设计和整机制造时请遵守安全标准并采取安全措施，以避免可能造成人身伤害或财产损失的情况！

Please Read Carefully

Thank you for using or about to use our company's products. We suggest that you carefully read this material before use.

- Our company strives to provide users with higher quality products and services.
- Jiangsu POWERSi Microelectronics Co., Ltd. will periodically optimize its products and corresponding specifications, and may not be able to notify you in a timely manner. Please download the latest version regularly.
- Jiangsu POWERSi Microelectronics Co., Ltd. assumes no responsibility or risk for any use of its products for special purposes.
- Jiangsu POWERSi Microelectronics Co., Ltd. holds patent rights for its own products.
- Any semiconductor product has a certain possibility of failure or malfunction under specific conditions. The buyer is requested to comply with safety standards and take safety measures when using products from Jiangsu POWERSi Microelectronics Co., Ltd. for system design and complete machine manufacturing, in order to avoid situations that may cause personal injury or property damage!