



Description

The FDD3706 uses advanced trench technology to provide excellent $R_{DS(ON)}$ and low gate charge .
The complementary MOSFETs may be used to form a level shifted high side switch, and for a host of other applications


General Features

$V_{DS} = 20V, I_D = 40A$
 $R_{DS(ON)} < 9 m\Omega @ V_{GS}=4.5V$


High power and current handling capability
Lead free product is acquired
Surface mount package

Application

- Power switching application
- Hard Switched and High Frequency Circuits
- Uninterruptible Power Supply



TO-252-2L
(DPAK)



N-Channel MOSFET

Ordering Information

Product ID	Pack	Brand	Qty(PCS)
FDD3706	TO-252-2L(DPAK)	HXY MOSFET	2500

Absolute Maximum Ratings@ $T_J=25^{\circ}C$ (unless otherwise specified)

Symbol	Parameter	Rating	Units
VDS	Drain-Source Voltage	20	V
VGS	Gate-Source Voltage	± 12	V
$I_D @ T_C=25^{\circ}C$	Drain Current, $V_{GS} @ 4.5V$	40	A
$I_D @ T_C=100^{\circ}C$	Drain Current, $V_{GS} @ 4.5V$	25	A
IDM	Pulsed Drain Current ¹	80	A
$P_D @ T_C=25^{\circ}C$	Total Power Dissipation	15.6	W
$P_D @ T_A=25^{\circ}C$	Total Power Dissipation ³	5	W
EAS	Single Pulse Avalanche Energy ⁴	150	mJ
TSTG	Storage Temperature Range	-55 to 150	$^{\circ}C$
T_J	Operating Junction Temperature Range	-55 to 150	$^{\circ}C$
Rthj-c	Maximum Thermal Resistance, Junction-case	8	$^{\circ}C/W$
Rthj-a	Maximum Thermal Resistance, Junction-ambient ³	25	$^{\circ}C/W$



Electrical Characteristics@T_j=25°C(unless otherwise specified)







Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	20	-	-	V
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =4.5V, I _D =20A	-	7.5	9	mΩ
		V _{GS} =2.5V, I _D =12A	-	9.1	12	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250uA	0.5	-	0.9	V
g _{fs}	Forward Transconductance	V _{DS} =5V, I _D =20A	-	50	-	S
I _{DSS}	Drain-Source Leakage Current	V _{DS} =16V, V _{GS} =0V	-	-	10	uA
I _{GSS}	Gate-Source Leakage	V _{GS} =±12V, V _{DS} =0V	-	-	±100	nA
Q _g	Total Gate Charge	I _D =20A	-	16	25.6	nC
Q _{gs}	Gate-Source Charge	V _{DS} =10V	-	3	-	nC
Q _{gd}	Gate-Drain ("Miller") Charge	V _{GS} =4.5V	-	4.5	-	nC
t _{d(on)}	Turn-on Delay Time	V _{DS} =10V	-	10	-	ns
t _r	Rise Time	I _D =1A	-	13	-	ns
t _{d(off)}	Turn-off Delay Time	R _G =3.3Ω	-	28	-	ns
t _f	Fall Time	V _{GS} =5V	-	7	-	ns
C _{iss}	Input Capacitance	V _{GS} =0V	-	1400	2240	pF
C _{oss}	Output Capacitance	V _{DS} =10V	-	170	-	pF
C _{rss}	Reverse Transfer Capacitance	f=1.0MHz	-	135	-	pF
R _g	Gate Resistance	f=1.0MHz	-	1	2	Ω
V _{SD}	Forward On Voltage ²	I _S =20A, V _{GS} =0V	-	-	1.2	V
t _{rr}	Reverse Recovery Time	I _S =12A, V _{GS} =0V,	-	8.5	-	ns
Q _{rr}	Reverse Recovery Charge	dI/dt=100A/μs	-	2.5	-	nC

Notes:

- 1.Pulse width limited by Max. junction temperature.
- 2.Pulse test
- 3.Surface mounted on 1 in² copper pad of FR4 board, t ≤10sec ; 60 °C/W at steady state.
- 4.Starting T_j=25°C , V_{DD}=20V , L=0.1mH , R_G=25Ω, V_{GS}=10V



Typical Characteristics






Fig 7. Gate Charge Characteristics




Fig 8. Typical Capacitance Characteristics




Fig 9. Maximum Safe Operating Area




Fig 10. Effective Transient Thermal Impedance




Fig 11. Transfer Characteristics




Fig 12. Gate Charge Waveform




Fig 13. Normalized BV_{DSS} v.s. Junction Temperature




Fig 14. Total Power Dissipation





Fig 15. Typ. Drain-Source on State Resistance



TO-252-2L(DPAK) Package Information



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min.	Max.	Min.	Max.
A	2.200	2.400	0.087	0.094
A1	0.000	0.127	0.000	0.005
b	0.660	0.860	0.026	0.034
c	0.460	0.580	0.018	0.023
D	6.500	6.700	0.256	0.264
D1	5.100	5.460	0.201	0.215
D2	0.483 TYP.		0.190 TYP.	
E	6.000	6.200	0.236	0.244
e	2.186	2.386	0.086	0.094
L	9.800	10.400	0.386	0.409
L1	2.900 TYP.		0.114 TYP.	
L2	1.400	1.700	0.055	0.067
L3	1.600 TYP.		0.063 TYP.	
L4	0.600	1.000	0.024	0.039
Φ	1.100	1.300	0.043	0.051
θ	0°	8°	0°	8°
h	0.000	0.300	0.000	0.012
V	5.350 TYP.		0.211 TYP.	



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only ; it is not guaranteed for volume production. HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.