



SILICON EPITAXIAL PLANAR DIODE

Fast Switching Diode

This diode is also available in MiniMELF case with the type designation LL4148



Glass Case DO-35
Dimensions in mm



Glass Case DO-34
Dimensions in mm

Absolute Maximum Ratings ($T_a = 25^\circ\text{C}$)

Parameter	Symbol	Value	Unit
Peak Reverse Voltage	V_{RM}	100	V
Reverse Voltage	V_R	75	V
Rectified Current (Average), Half Wave Rectification with Resist. Load at $f \geq 50$ Hz	I_O	150 ¹⁾	mA
Surge Forward Current at $t < 1$ s and $T_j = 25^\circ\text{C}$	I_{FSM}	500	mA
Power Dissipation	P_{tot}	500 ¹⁾	mW
Junction Temperature	T_j	200	$^\circ\text{C}$
Storage Temperature Range	T_S	- 65 to + 200	$^\circ\text{C}$


¹⁾ Valid provided that leads at a distance of 8 mm from case are kept at ambient temperature.

1N4148

Characteristics at $T_j = 25^\circ\text{C}$

Parameter	Symbol	Min.	Max.	Unit
Forward Voltage at $I_F = 10\text{ mA}$	V_F	-	1	V
Leakage Current at $V_R = 20\text{ V}$ at $V_R = 75\text{ V}$ at $V_R = 20\text{ V}$, $T_j = 150^\circ\text{C}$	I_R I_R I_R	- - -	25 5 50	nA μA μA
Reverse Breakdown Voltage at $I_R = 100\text{ }\mu\text{A}$ at $I_R = 5\text{ }\mu\text{A}$	$V_{(BR)R}$ $V_{(BR)R}$	100 75	- -	V V
Capacitance at $V_F = V_R = 0$	C_{tot}	-	4	pF
Voltage Rise when Switching ON tested with 50 mA Forward Pulses $t_p = 0.1\text{ s}$, Rise Time < 30 ns, $f_p = 5\text{ to }100\text{ KHz}$	V_{fr}	-	2.5	V
Reverse Recovery Time from $I_F = 10\text{ mA}$ to $I_R = 1\text{ mA}$, $V_R = 6\text{ V}$, $R_L = 100\text{ }\Omega$	t_{rr}	-	4	ns
Thermal Resistance Junction to Ambient Air	R_{thA}	-	0.35 ¹⁾	K/mW
Rectification Efficiency at $f = 100\text{ MHz}$, $V_{RF} = 2\text{ V}$	η_v	0.45	-	-


¹⁾ Valid provided that leads at a distance of 8 mm from case are kept at ambient temperature.




Rectification Efficiency Measurement Circuit

1N4148


Forward characteristics




Dynamic forward resistance versus forward current



Admissible power dissipation versus ambient temperature
Valid provided that leads at a distance of 8 mm from case are kept at ambient temperature



Relative capacitance versus reverse voltage



1N4148

