


Features

- Low $R_{DS(on)}$ @ $V_{GS}=-4.5V$
- -5V Logic Level Control
- P Channel SOT-23 Package
- Pb-Free, RoHS Compliant

Key Items	PMOS	Unit
BVDSS	-30	V
ID	-4.2	A
$R_{DS(on)}$ @-4.5V	55	mΩ

Applications

- DC Fan
- Charger, Fast switch
- Optimized for Power
- Management Applications for Portable Products, such as H-bridge, Inverters Car Charger and Others

**SOT23****Order Information**

Product	Package	Marking	Packing	Min Unit Quantity
AO3401	SOT-23	R1	3000PCS/Reel	3000PCS

Absolute Maximum Ratings

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

may affect device reliability.

Symbol	Parameter	Rating	Unit	
Common Ratings (TA=25°C Unless Otherwise Noted)				
VGS	Gate-Source Voltage	±12	V	
V(BR)DSS	Drain-Source Breakdown Voltage	-30	V	
TJ	Maximum Junction Temperature	150	°C	
TSTG	Storage Temperature Range	-50 to 150	°C	
Mounted on Large Heat Sink				
IDM	Pulse Drain Current Tested①	TA=25°C	-16.8	A
ID	Continuous Drain Current(VGS=-4.5V)	TA=25°C	-4.6	A
		TA=70°C	-3.5	
PD	Maximum Power Dissipation	TA=25°C	1.2	W
		TA=70°C	0.9	
RJA	Thermal Resistance Junction-Ambient	100	°C/W	

Symbol	Parameter	Condition	Min	Typ	Max	Unit
Static Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
V _{(BR)DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V I _D =-250μA	-30	--	--	V
I _{DSS}	Zero Gate Voltage Drain Current(T _A =25°C)	V _{DS} =-24V, V _{GS} =0V	--	--	-1	μA
	Zero Gate Voltage Drain Current(T _A =125°C)	V _{DS} =-24V, V _{GS} =0V	--	--	-100	uA
I _{GSS}	Gate-Body Leakage Current	V _{GS} =±12V, V _{DS} =0V	--	--	±100	nA
V _{GS(TH)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =-250μA	-0.5	-0.7	-1.5	V
R _{DS(ON)}	Drain-Source On-State Resistance②	V _{GS} =-4.5V, I _D =-4.6A	--	55	70	mΩ
R _{DS(ON)}	Drain-Source On-State Resistance②	V _{GS} =-3.3V, I _D =-2A	--	65	85	mΩ
Dynamic Electrical Characteristics @ T _J = 25°C (unless otherwise stated)						
C _{iss}	Input Capacitance	V _{DS} =-15V, V _{GS} =0V, f=1MHz	--	710	--	pF
C _{oss}	Output Capacitance		--	90	--	pF
C _{rss}	Reverse Transfer Capacitance		--	40	--	pF
Q _g	Total Gate Charge	V _{DS} =-15V I _D =-4A, V _{GS} =-4.5V	--	8.5	--	nC
Q _{gs}	Gate Source Charge		--	1	--	nC
Q _{gd}	Gate Drain Charge		--	1.7	--	nC
Switching Characteristics @ T _J = 25°C (unless otherwise stated)						
t _{d(on)}	Turn on Delay Time	V _{DD} =-15V, I _D =-4A, R _G =3.3Ω, V _{GS} =-4.5V	--	8.5	--	ns
t _r	Turn on Rise Time		--	5.5	--	ns
t _{d(off)}	Turn Off Delay Time		-	26	--	ns
t _f	Turn Off Fall Time		--	12.5	--	ns
Source Drain Diode Characteristics						
I _{SD}	Source drain current(Body Diode)	T _A =25°C	--	--	-1.5	A
V _{SD}	Forward on voltage②	T _J =25°C, I _{SD} =-4A, V _{GS} =0V	--	-0.85	-1.2	V

Notes: ① Pulse width limited by maximum allowable junction temperature

②Pulse test ; Pulse width 300 μs, duty cycle 2%.

Typical Characteristics




Fig1. Typical Output Characteristics




Fig3. Typical Transfer Characteristics




Fig5. Typical Source-Drain Diode Forward Voltage




Fig2. Normalized Threshold Voltage Vs. Temperature




Fig4. Drain-Source Voltage vs Gate-Source Voltage




Fig6. Maximum Safe Operating Area

Typical Characteristics




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage




Fig9. Normalized Maximum Transient Thermal Impedance




Fig10. Switching Time Test Circuit and waveforms