





RoHs

General tolerances (mm)														0.1/10 ±2°
0 3	>3 6	>6 10	>10 18	>18 30	>30 50	>50 80	>80 120	>120 180	>180 250	>250 315	>315 400	>400 500	>500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50	

Product model	PIN	A	B	C
HMT-EDGVC-3.81-1-2PGG	2	3.81	8.41	3.81
HMT-EDGVC-3.81-1-3PGG	3	7.62	12.22	7.62
HMT-EDGVC-3.81-1-4PGG	4	11.43	16.03	11.43
HMT-EDGVC-3.81-1-5PGG	5	15.24	19.84	15.24
HMT-EDGVC-3.81-1-6PGG	6	19.05	23.65	19.05
HMT-EDGVC-3.81-1-7PGG	7	22.86	27.46	22.86
.....				
HMT-EDGVC-3.81-1-24PGG	24	3.81x (N-1)	3.81xN+0.79	3.81x (N-1)

UL Standard		B	C	D
Rated Voltage (V)/Current (A)		300/8	/	300/8
IEC Standard				
Overvoltage Category/Pollution Degree		II /2		
Rated Voltage (V)/Current (A)		250/7		
Rate Impulse Voltage (KV)		2.5		
Pitch (mm)/Poles		3.81/N=02~24P		
Operating temperature (° C)		-40~+105		
Conform to RoHS		Yes		

2	Pin	Copper alloy	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCES UNLESS SPECIFIED		 深圳市华明通电子有限公司 HMTCONN Shenzhen Huamingtong Electronics Co., Ltd	
		PART NO. HMT-EDGVC-3.81-1-NPGG	TITLE: Socket-type terminal
		DESIGN: James	CUSTOMER
		CHED: Talen	SIZE A4
		APPD: Sophia	UNITS MM
MANUFACTURE DWG			SCALE N:A
			SHEET 1/1