


TLCMI3225B-2-101TF

Wire Wound Chip Common Mode Choke Coil

TOP-EMC

Feature

- Winding type realizes small size and low profile
- Prevention of common mode noise at high Frequency
- Min 2200Ω are optional for different noise level and signal frequency
- Excellent soldering heat resistance
- Operating Temp:-40°C+125°C
- Compliant with AEC-Q200



Application

- CAN-FD
- Fax AND ISDN
- Modem
- A² B

Part Number System

TLCMI 3225B -2 -101 T F
① ② ③ ④ ⑤ ⑥

- ① Type : TLCMI
- ② External Dimensions (L×W) (mm) : 3.2X2.5
- ③ Number of Lines : 2
- ④ Inductance : 101=100uH
- ⑤ Packing : Tape & Reel
- ⑥ F : Hazardous Substance Free Products

Specifications



Part Number	Inductance	DC Resistance	Rated Current	Rated Voltage	Insulation Resistance
	L (uH)	DCR (Ω)	Ir (mA)	V _{DC} (V)	IR (M Ω)
	+50%/-30%, 100KHz/0.1V	Max	Max	Max	Min
TLCMI3225B-2-101TF	100	1.5	150	50	10

1. Rated Current Applied the current to coils, the temperature rise shall not be more than $\Delta T \leq 40^\circ\text{C}$


2. Operating Temperature: $-40 \sim +125^\circ\text{C}$, Storage Temperature: -10 to $+40^\circ\text{C}$, 30~70%RH

Typical Electrical Characteristics


■ Impedance VS. Frequency Characteristics




■ Sdd21




■ Scc21




■ Ssd21




■ Ssd12




Shape And Dimensions



Land Pattern (mm)




Schematics (Bottom)



A(mm)	B(mm)	C(mm)	E(mm)	D1(mm)	D2(mm)	F(mm)	G(mm)	I(mm)	H(mm)
3.2±0.2	2.5±0.2	2.5Max	0.2Typ.	0.8Typ.	0.9Typ.	4.0Typ.	2.8Typ.	0.6Typ.	1.6Typ.

Recommended Soldering Technologies



Item.	Ramp - up	Preheating	Reflow	Peak Temp	Cooling
Temp.scope	R.T.~150°C	150°C~200°C	217°C	245±5°C	Peak Temp.~150°C
Time spec	——	60~180 sec	60~150sec	20~40sec	——
Time result	——	70~95 sec	70~95sec	20~35sec	——

CONTACT INFORMATION

SHENZHEN TOP-FLIGHT TECHNOLOGY CO.,LTD

4th Floor, C Building, Yuanfen Industrial Park , Bulong Road, Longhua New District,
Shenzhen Tel: 86 -755- 82908191 Fax: 86-755- 82908701 Email: kang@topleve.com

Website: <http://www.topleve.com>