






RoHs

General tolerances (mm)

$0 \sim 3$	$>3 \sim 6$	$>6 \sim 10$	$>10 \sim 18$	$>18 \sim 30$	$>30 \sim 50$	$>50 \sim 80$	$>80 \sim 120$	$>120 \sim 180$	$>180 \sim 250$	$>250 \sim 315$	$>315 \sim 400$	$>400 \sim 500$	>500	$0.1/10$
± 0.12	± 0.18	± 0.22	± 0.26	± 0.31	± 0.37	± 0.57	± 0.80	± 0.93	± 1.05	± 1.15	± 1.60	± 2.20	± 2.50	$\pm 2^\circ$



PCB LAYOUT

Product model	PIN	A	B	C
HMT-EDGVC-5.08-1-2PMG	2	12.16	5.08	5.08
HMT-EDGVC-5.08-1-3PMG	3	17.24	10.16	10.16
HMT-EDGVC-5.08-1-4PMG	4	22.32	15.24	15.24
HMT-EDGVC-5.08-1-5PMG	5	27.40	20.32	20.32
HMT-EDGVC-5.08-1-6PMG	6	32.48	25.40	25.40
HMT-EDGVC-5.08-1-7PMG	7	37.56	30.48	30.48
.....				
HMT-EDGVC-5.08-1-24PMG	24	5.08xN+2	5.08x(N-1)	5.08x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	III/3	III/2	II/2
Rated Voltage(V)/Current(A)	/	320/20	/
Rate Impulse Voltage(KV)	/	4	/
Pitch(mm)/Poles	5.08/N=02~24P		
Operating temperature(°C)	-40°C~+105°C		
Conform to RoHS	Yes		

2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

GENERAL TOLERANCES
UNLESS SPECIFIED

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-EDGVC-5.08-1-NPMG

TITLE:
Socket-type terminal

DESIGN: James

CUSTOMER

SIZE
A4


UNITS
MM

CHED: Talen

SCALE

SHEET

APPD: Sophia



N:A
1/1