




RoHs

NOTES:

1. BASE: LCP
2. PIN: Brass
3. Solder Tab: Brass


SPECIFICATIONS:

1. Spacing: 2.0
2. Voltage Rating: 250V AC DC
3. Current Rating: 2A AC DC
4. Insulation Resistance: 800M Ω Min
5. Contact Resistance: 20m Ω Max
6. Withstanding voltage: 500V AC 1/Minute
7. Temperatuer Range: -25 $^{\circ}$ C ~+ 85 $^{\circ}$ C



PIN number variable size comparison table

PART NO	Pin	A	B	C	D
HMT-HY2.0-WT2P	2	2.00	8.00	2.50	4.90
HMT-HY2.0-WT3P	3	4.00	10.00	2.50	6.90
HMT-HY2.0-WT4P	4	6.00	12.00	5.00	8.90
HMT-HY2.0-WT5P	5	8.00	14.00	7.00	10.90
HMT-HY2.0-WT6P	6	10.00	16.00	9.00	12.90
HMT-HY2.0-WT7P	7	12.00	18.00	11.00	14.90
.....					
HMT-HY2.0-WT16P	16	30.00	36.00	29.00	32.90



GENERAL TOLERANCES
UNLESS SPECIFIED

X.X	±0.30	X.°	±5°
.XX	±0.20	X.X°	±1°
.XXX	±0.10	X.XX°	±0.5°

MANUFACTURE DWG



深圳市华明通电子有限公司
Shenzhen Huamingtong Electronics Co., Ltd

PART NO.
HMT-HY2.0-WTNP
DESIGN: James
CHED: Talen
APPD: Sophia

TITLE:
WAFER 2.00 卧贴带扣
CUSTOMER
SIZE
A4
UNITS
MM
SCALE
N:A
SHEET
1/1