




Surface Mount Fast Recovery Rectifiers

Features

- Top-side Cooling(TSC) Packaging technology
- Compact and Slim Packaging Solutions
- For surface mounted applications
- Fast reverse recovery time
- Lead free in comply with EU RoHS 2011/65/EU directives

Mechanical Data

- Case: SMHS
- Terminals: leads solderable per MIL-STD-750, Method 2026
- Polarity: Color band denotes cathode end



Ordering Information

Part Number	Shipping	Reel
LTR1AS THRU LTR1MS	15000PCS Tape&Reel	13 inchs

Absolute Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60Hz, resistive or inductive load, for capacitive load current derate by 20%.

Parameter	Symbol	LTR1AS	LTR1BS	LTR1DS	LTR1GS	LTR1JS	LTR1KS	LTR1MS	Unit
	Marking	R1A	R1B	R1D	R1G	R1J	R1K	R1M	
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	800	1000	V
Maximum average forward rectified current @ Fig.1	I _{F(AV)}	1							A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	30							A
Maximum instantaneous forward voltage at 1.0A	V _F	1.3							V
Maximum DC reverse current T _A =25°C at rated DC reverse voltage T _A =100°C	I _R	1 50							μA
Typical junction capacitance (Note1)	C _j	15							pF
Maximum reverse recovery time (Note2)	t _{rr}	150				250	500		ns
Typical thermal resistance (Note3)	R _{θJA} R _{θJC}	65 7							°C/W
Operating and StorageTemperature Range	T _j , T _{stg}	-55 to +150							°C

Note: (1) Measured at 1 MHz and applied reverse voltage of 4 V D.C

(2) Measured with $I_F = 0.5 A$, $I_R = 1 A$, $t_{rr} = 0.25 A$.

(3) P.C.B. mounted with 0.08" × 0.08" (2mm × 2mm) copper pad areas.



Characteristics Curves

FIG.1 FORWARD CURRENT DERATING CURVE




FIG.2 TYPICAL REVERSE CHARACTERISTICS




FIG.3 TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




Fig. 4 TYPICAL JUNCTION CAPACITANCE






FIG.5 MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT



Package Outline

SMHS

Unit : mm




UNIT		A	C	D	E	H _E	d	e	f	h	∠
mm	max	0.99	0.25	2.90	2.10	3.50	1.30	1.30	1.25	0.70	6°
	min	0.83	0.15	2.50	1.70	2.90	1.10	1.10	1.05	0.50	

Suggested Pad Layout

SMHS

Unit : mm




Note:

1. Controlling dimension: in millimeters.
2. General tolerance: $\pm 0.05\text{mm}$
3. The pad layout is for reference purpose only.



Carrier Tape Dimensions

Unit : mm





Symbol	Spec	Symbol	Spec
W	8.00±0.10	P2	2.00±0.10
E	1.75±0.10	t	0.22±0.02
F	3.50±0.10	t1	Min. 0.05
D0	1.55±0.10	A0	2.15±0.10
D1	1.10±0.10	B0	3.40±0.10
P0	4.00±0.10	K0	1.15±0.10
P1	4.00±0.10		

Reel Dimensions

Unit : mm

13" Reel




D5	Φ330.0±5.0
D6	Φ13.5±0.5
H	2.5±1.0
W2	8.0±2.0
Quantity: 15000PCS	


Packaging



15000 PCS/Reel



5 Reel/Inner Box
75K PCS/Inner Box



Dim(Unit:mm)
340mm*340mm*85mm

Dim(Unit:mm)
360mm*360mm*355mm




4 Boxes per carton
300K PCS per carton

13 inches Reel



Recommended Soldering Conditions



Recommended Conditions

Profile Feature	Pb-Free Assembly
Average ramp-up rate (T_L to T_P)	3°C/second max.
Preheat	
-Temperature Min ($T_{S\ min}$)	150°C
-Temperature Max ($T_{S\ max}$)	200°C
-Time (min to max) (t_S)	60-180 seconds
$T_{S\ max}$ to T_L	
-Ramp-up Rate	3°C/second max.
Time maintained above:	
-Temperature (T_L)	217°C
-Time (t_L)	60-150 seconds
Peak Temperature (T_P)	260°C
Time within 5°C of actual Peak Temperature (t_P)	20-40 seconds
Ramp-down Rate	6°C/second max.
Time 25°C to Peak Temperature	8 minutes max.

Important Notice and Disclaimer

Leading-Tech reserves the right to make changes to this document and its products and specifications at any time without notice.

Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

Leading-Tech makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Leading-Tech assume any liability for application assistance or customer product design.

Leading-Tech does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of Leading-Tech.

Leading-Tech products are not authorized for use as critical components in life support devices or systems without express written approval of Leading-Tech.

Version Update Information

Series NO.	Enactment/Revision Date	Effective Date	Version	Revision Content	Revision Reason	Revision Person	Note
01	2025.09.09	2025.09.09	1.0	New file	/	Ding	